

- Very high deformation allowing high levels of energy to be absorbed
- Progressive deformation
- Materials:
 - Core: Stainless steel plates (A2)
 - Head: Rubber
- **Hardness: NK 55-60 Shore A**
- Working temp: -40°C to +70°C

Uses


- Shock absorbing stop

Info.

- **Not sold individually, please contact us for details**
- Load and stiffness figures are given as a guide only



stainless steel



DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc. List	-	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	Compression Stiffness (N/mm)	Max load (N)	Stock*	Price each 1 to 5
E-ZY4-10-10/SS	M4	10	10	38	43	✓	2,54 €
E-ZY4-10-15/SS	M4	10	15	-	-	✓	1,98 €
E-ZY4-15-15/SS	M4	15	15	74	95	✓	2,16 €
E-ZY6-20-15/SS	M6	20	15	138	170	✓	2,87 €
E-ZY6-20-20/SS	M6	20	20	-	-	✓	3,00 €
E-ZY6-25-10/SS	M6	25	10	-	-	✓	3,15 €
E-ZY6-25-20/SS	M6	25	20	128	280	✓	3,38 €
E-ZY6-25-30/SS	M6	25	30	80	280	✓	4,00 €
E-ZY8-30-15/SS	M8	30	15	-	-	✓	4,00 €
E-ZY8-30-17/SS	M8	30	17	-	-	✓	4,00 €
E-ZY8-30-20/SS	M8	30	20	200	400	✓	4,46 €
E-ZY8-30-30/SS	M8	30	30	120	400	✓	5,42 €
E-ZY8-40-30/SS	M8	40	30	23	234	✓	6,66 €
E-ZY10-50-20/SS	M10	50	20	680	1000	✓	8,48 €
E-ZY10-50-30/SS	M10	50	30	425	1000	✓	9,22 €
E-ZY10-50-40/SS	M10	50	40	-	-	✓	10,06 €
E-ZY10-50-50/SS	M10	50	50	-	-	✓	11,89 €
E-ZY12-75-25/SS	M12	75	25	2000	2300	-	18,20 €
E-ZY12-75-55/SS	M12	75	55	-	-	-	26,69 €

*Depending on availability - Dimensions in mm

Our other products




RDE-N

Sealing washer
Hygienic Usit®,
Stainless steel - Black
EPDM




PTMR

Telescopic furniture
foot, threaded stud



H1

Crossed helical gear
crossed axis at 90°,
Machined plastic
(delrin)



PTBss

Threaded eye hook
stainless steel,
Stainless steel



PR85

Articulated foot Ø83,
Ø 83



AT5P_AT10P

Connecting plate for
AT type timing belts,
AT10



HRV

V-rail guidance
Simple Select®
system, Rail with
carriage



LVT

Miniature motorised
actuator 2A, 2 amperes



BH01

Single housed
bearing, Bearing fitted



PTA80

Articulated levelling
foot, pressed base



CHINV2

Invisible hinge,
Invisible - Opening up



BGC

Oldham coupling,
Clamp

Complementary products



EZY

Cylindrical stop, Steel



DZYSS

Stainless steel
cylindrical stop,
stainless steel