

# Long hinge in steel or aluminium **AluSte**

## CHAL

## Piano type hinge

- Long hing with a small pin diameter
- Rolled joint
- Hinge is not drilled
- Materials:
  - Untreated steel
  - Aluminium

**Economical**





### Applications

- Woodworking, industrial joinery, workstations...

### Advantages

- Compact design
- Possibility of cutting to the length desired



Typical application

### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-5%	On request

Part number	A	L	P	E	ØN	Weight per metre (kg/m)	Price each 1 to 5
<b>Steel</b>							
CHAL3-40-1000	40	1000	20	1,2	3	0,530	12,33 €
CHAL3-50-1000	50	1000	20	1,2	3	0,610	12,98 €
<b>Aluminium</b>							
CHAL3-35-1000/A	35	1000	20	1,0	3	0,175	14,37 €
CHAL3-40-1000/A	40	1000	20	1,0	3	0,208	14,56 €
CHAL4-50-1000/A	50	1000	30	1,5	4	0,300	18,95 €

Dimensions in mm

- Long hinge with a small pin diameter
- Rolled joint
- Hinge is not drilled
- Material:  
304 stainless steel

Economical





### Applications

- Woodworking, industrial joinery, workstations...

### Advantages

- Compact design
- Possibility of cutting to the length desired



Typical application

### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-5%	On request

Part number	A	L	P	E	ØN	Weight per metre (kg/m)	Stock*	Price each 1 to 5
CHAL2-20-1000/SS	20	1000	15	0,6	2,5	0,140	✓	17,09 €
CHAL2-25-1000/SS	25	1000	15	0,6	2,5	0,165	-	17,11 €
CHAL2-30-1000/SS	30	1000	15	0,6	2,5	0,190	-	18,10 €
CHAL3-25-1000/SS	25	1000	20	1,0	3,0	0,325	✓	18,26 €
CHAL3-40-1000/SS	40	1000	20	1,2	3,0	0,520	✓	24,88 €
CHAL3-50-1000/SS	50	1000	20	1,2	3,0	0,620	✓	26,87 €
CHAL6-60-1000/SS	60	1000	30	2,0	6,0	1,470	✓	66,33 €
CHAL6-80-1000/SS	80	1000	30	2,0	6,0	1,700	-	75,93 €

Dimensions in mm

## Our other products



KB\_UU  
Closed linear  
precision bearing,  
Precision - steel



TCXR  
Automatic chain  
tensioner, With steel  
sprocket




MAX26  
Motor-gearbox 12V  
and 24V DC, from  
0,075 to 0,6Nm



RT61ss  
Self-centering locking  
Assembly,  
Medium/low torque



ACL  
Joints for aluminium  
profiles, Variable  
angle corner



BMF  
Knurled knob -  
female, Knurled -  
through threaded



AFSE  
Locking pin with  
interlocking safety  
latch, with  
interlocking safety...



PGM52-M4  
Pull handle,  
Aluminium



LVT  
Miniature motorised  
actuator 4A, 4 amperes



M  
Bellows cover,  
Accessory:



LVT  
Miniature motorised  
actuator 4A, 4 amperes



M0  
Worm and wheel set,  
Bronze

## Complementary products



CHAL3  
Piano hinge, Steel