

Weld-on hinge with flat end

New

CHAPAM

In steel

- Weld-on hinge
- Flat ends
- Materials:
 - Steel
 - Brass washer


Advantage

- Easy demounting of the door or the leaf



Uses

- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets

NEW!



Example of use



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Price	-10%	-20%	On request

Part number	L	ØD	S	F	ØG	Price each 1 to 5
CHAPAM60-10	60	10	12,0	19,5	6	2,12 €
CHAPAM80-13	80	13	16,0	23,0	7	2,54 €
CHAPAM100-16	100	16	20,0	27,0	9	4,85 €
CHAPAM120-16	120	16	20,0	27,0	9	5,50 €
CHAPAM140-20	140	20	25,3	34,0	11	9,07 €
CHAPAM160-20	160	20	25,3	43,0	12	10,44 €
CHAPAM180-20	180	20	25,3	53,0	13	13,32 €

Dimensions in mm

New

Weld-on hinge with flat end

In **stainless steel** or aluminium **CHAPAM**

- **Weld-on hinge**
- Flat ends
- Materials:
Stainless steel 304, washer stainless steel
Aluminium, washer stainless steel

Advantage

- Easy demounting of the door or the leaf


Uses

- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets



NEW!

Aluminium

Stainless steel



Example of use

**DISCOUNTS**

Qty	1+	6+	20+	50+
Disc. Price	-10%	-20%	On request	

Part number	L	ØD	S	F	ØG	Price each 1 to 5
Stainless steel						
CHAPAM60-10/SS	60	10	12	19,5	6	12,90 €
CHAPAM80-13/SS	80	13	16	23,0	7	16,50 €
CHAPAM100-16/SS	100	16	20	27,0	9	26,25 €
Aluminium						
CHAPAM80-13/AA	80	13	16	23,0	7	11,45 €
CHAPAM100-16/AA	100	16	20	27,0	9	15,01 €
CHAPAM120-16/AA	120	16	20	27,0	9	17,39 €

Dimensions in mm

Our other products



PCS6ECO
Chain sprocket - steel,
6mm (DIN 04-1)



BPHR
Ball transfer unit
housed spring loaded,
High



AT5M AT10M
AT type timing belt
per metre, AT5 Steel
cored polyurethane




NCT
Square tube
connector, Fixed
angle



AC
Strike for toggle latch,
13mm



PTAF100-PAMF100
Articulated fixable
foot with pressed
base Ø100, Ø 100



PRZ
Wear strip for slat top
chain, Z profile to be
clipped



G4-ECO
Eco range Spur gear,
Steel C45



BPPE
Ball transfer unit push
fit, Light



MDB_MTB
Moulded plastic bevel
gear (nylon), 2:1



STRIPF
Sealing brush strip,
1m length



CLSCLP_SS
Clevis components,
short version,
Stainless steel - short
range

Complementary products



CHAPAMss
Weld-on hinge with
flat end, Stainless
steel or Aluminium