

Weld-on hinge with flat end

CHAPAM

In steel


- **Weld-on hinge**
- Flat ends
- Materials:
 - Steel
 - Brass washer

Advantage



- Easy demounting of the door or the leaf

Uses

- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets



Example of use



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Price	-10%	-20%	On request

Part number	L	ØD	S	F	ØG	Price each 1 to 5
CHAPAM60-10	60	10	12,0	19,5	6	3,93 €
CHAPAM80-13	80	13	16,0	23,0	7	5,02 €
CHAPAM100-16	100	16	20,0	27,0	9	7,62 €
CHAPAM120-16	120	16	20,0	27,0	9	8,95 €
CHAPAM140-20	140	20	25,3	34,0	11	10,18 €
CHAPAM160-20	160	20	25,3	43,0	12	17,57 €
CHAPAM180-20	180	20	25,3	53,0	13	22,42 €

Dimensions in mm

Weld-on hinge with flat end

In **stainless steel** or aluminium **CHAPAM**



- **Weld-on hinge**
- Flat ends
- Materials:
Stainless steel 304, washer stainless steel
Aluminium, washer stainless steel

Advantage



- Easy demounting of the door or the leaf

Uses

- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets



Example of use



DISCOUNTS

Qty	1+	6+	20+	50+
Disc. Price	-10%	-20%	On request	

Part number	L	ØD	S	F	ØG	Price each 1 to 5
Stainless steel						
CHAPAM60-10/SS	60	10	12	19,5	6	16,45 €
CHAPAM80-13/SS	80	13	16	23,0	7	23,14 €
CHAPAM100-16/SS	100	16	20	27,0	9	36,82 €
Aluminium						
CHAPAM80-13/AA	80	13	16	23,0	7	10,28 €
CHAPAM100-16/AA	100	16	20	27,0	9	14,32 €
CHAPAM120-16/AA	120	16	20	27,0	9	15,61 €

Dimensions in mm


Weld-on

CHAGC_{SS} CHAGD_{SS}

- To be welded
- Materials:
Body: stainless steel 316
Pin: stainless steel


Advantage

- Allows easy removal of the opening part



CHA-GC

centred hinge plates



CHA-GD

offset hinge plates

DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	Description	Stock*	Price each 1 to 5
CHA-GC-9/SS	Centred hinge plates	✓	20,67 €
CHA-GD-9/SS	Offset hinge plates	✓	19,85 €

*Depending on availability - Dimensions in mm

Screw-on lift-off hinge

Alu Stock

CHAGC/AL

Anodised aluminium

- **Screw-on hinge**
- Opening angle 270°
- Materials:
 - Aluminium 6060 T5
 - Stainless steel spindle
 - Plastic caps

Advantage

- Reduced space requirement
- Lift-off


Space saving




Clear anodised



Black anodised



Type 1



Type 2

DISCOUNTS


Qty	1+	6+	20+	50+
Disc	Net	-5%	-10%	On request

Part number	Type	Finish	A	B	C	ØD	E	Weight (g)	Stock*	Price each
									1 to 5	
CHA-GC-9-1/AL/IN	1	Clear anodised	102	45,9	2,5	6,1	50	50	✓	19,79 €
CHA-GC-9-2/AL/IN	2	Clear anodised	102	45,9	2,5	6,1	50	50	-	19,79 €
CHA-GC-9-1/AL/BK	1	Black anodised	102	45,9	2,5	6,1	50	50	✓	20,69 €
CHA-GC-9-2/AL/BK	2	Black anodised	102	45,9	2,5	6,1	50	50	✓	19,79 €

*Depending on availability - Dimensions in mm

- Polished finish
- Screw fixing
- Material: stainless steel 304

stainless steel



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	Description	Stock*	Price each 1 to 5
CHA-GC-14/SS	Centred hinge plates	✓	48,59 €

*Depending on availability - Dimensions in mm