

# Weld-on hinge with flat end

New

## CHAPAM

In steel


- Weld-on hinge
- Flat ends
- Materials:
  - Steel
  - Brass washer

### Advantage


- Easy demounting of the door or the leaf

### Uses


- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets



Example of use



NEW!



### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Price	-10%	-20%	On request

Part number	L	ØD	S	F	ØG	Price each 1 to 5
CHAPAM60-10	60	10	12,0	19,5	6	2,12 €
CHAPAM80-13	80	13	16,0	23,0	7	2,54 €
CHAPAM100-16	100	16	20,0	27,0	9	4,85 €
CHAPAM120-16	120	16	20,0	27,0	9	5,50 €
CHAPAM140-20	140	20	25,3	34,0	11	9,07 €
CHAPAM160-20	160	20	25,3	43,0	12	10,44 €
CHAPAM180-20	180	20	25,3	53,0	13	13,32 €

Dimensions in mm

**New**

# Weld-on hinge with flat end

**In stainless steel or aluminium CHAPAM**

- **Weld-on hinge**
- Flat ends
- Materials:  
Stainless steel 304, washer stainless steel  
Aluminium, washer stainless steel

**Advantage**

- Easy demounting of the door or the leaf


**Uses**

- Metal doors
- Armoured doors
- Machine tool doors
- Electrical cabinets



**NEW!**

Aluminium

Stainless steel



Example of use

**DISCOUNTS**

Qty	1+	6+	20+	50+
Disc. Price	-10%	-20%	On request	

Part number	L	ØD	S	F	ØG	Price each 1 to 5
<b>Stainless steel</b>						
CHAPAM60-10/SS	60	10	12	19,5	6	12,90 €
CHAPAM80-13/SS	80	13	16	23,0	7	16,50 €
CHAPAM100-16/SS	100	16	20	27,0	9	26,25 €
<b>Aluminium</b>						
CHAPAM80-13/AA	80	13	16	23,0	7	11,45 €
CHAPAM100-16/AA	100	16	20	27,0	9	15,01 €
CHAPAM120-16/AA	120	16	20	27,0	9	17,39 €

Dimensions in mm

## Our other products



BCAss  
Stainless steel splined bush, Inox



PSG15S  
Spur gear - precision range, Stainless steel 316



T10\_30\_AL  
T type timing pulley, Economy range - T10 aluminium



CNA-CNG  
Right angled mounting plate, Right angled mounting plate for ball jo...



BABpss  
301 Stainless steel ball pin, Stainless steel




UCP\_PBT  
Stainless/Polymer pillow block bearing, Polymer and stainless steel




NT92  
Spur gear coaxial gearbox, from 15 to 40 Nm - In-line



EAR  
Bearing locknut, Self locking locknut - nylon lock washer



INO  
Internal gear, Machined plastic



VKM  
Square steel nut, Steel - 1 thread



HBM  
Adjustment bushing for half-rail guide,



UCF  
Cast iron flange bearing unit, Cast iron

## Complementary products



CHAPAM  
Weld-on hinge with flat end, Steel