



Flat profile - Round guide

For bottling and packaging applications


GMC
GMCss

- Guide profile for conveying products
- Materials:
 - Guide: DESLIDUR polyethylene (UHMW1000)
 - Support: steel or stainless steel
- Green


Accessories

- GMC-BR fixing clips (tome 5 p.114)
- SDG supports (tome 5 p.122)

Suitable for guiding many different products



Typical application



DISCOUNTS

Qty	1+	2+	4+	10+
Disc.	List	-10%	-15%	On request

Part number	Length (mm)	Support material	Weight (kg/m)	Stock*	Price each
GMC20-3000	3000	Steel	0,70	✓	57,28 €
GMC20-3000/SS	3000	Stainless steel	0,70	✓	89,11 €

*Depending on availability - Dimensions in mm

Flat guide for conical profile



GMK17Pss



For bottling and packaging applications

- Guide profile for conveying products
- Materials:
Guide: DESLIDUR polyethylene (UHMW1000)
Support: stainless steel



Accessories

- GMK17-BR (tome 5 p.114), GMK17-BRS/SS, GMK17-BRD/SS fixing clip (tome 5 p.117)118
- SDG support (tome 5 p.122)
- GMK17-RG/SS link (tome 5 p.116)



Typical application:
guiding food cartons

DISCOUNTS

Qty	1+	2+	4+	10+
Disc.	List	-10%	-15%	On request

Part number	Colour	H	Length L(mm)	Weight (kg/m)	Stock*	Price each
GMK17-P40-3/SS	White	40	3000	0,88	✓	143,94 €
GMK17-P50-2/SS	White	50	2000	0,95	-	231,10 €
GMK17-P60-2/SS	White	60	2000	1,02	✓	174,38 €

*Depending on availability - Dimensions in mm



Round guide for conical profile



For bottling and packaging applications

GMK17RSS

- Guide profile for conveying products
- Materials:
Guide: DESLIDUR Polyethylene (UHMW1000)
Support: stainless steel

Accessories

- GMK17-BR (tome 5 p.114), GMK17-BRS/SS, GMK17-BRD/SS fixing clip (tome 5 p.117)
- SDG support (tome 5 p.122)
- GMK17-RG/SS link (tome 5 p.116)



Typical application:
guiding bottles

DISCOUNTS

Qty	1+	2+	4+	10+
Disc.	List	-10%	-15%	On request

Part number	Colour	Length L (mm)	Weight (kg/m)	Stock*	Price each
GMK17R-3/SS	White	3000	0,67	✓	95,05 €

*Depending on availability - Dimensions in mm