




CLM CLM_{SS}

Steel or stainless steel

- Clevis link
- Threaded end piece for clevis conforming to **DIN71752, short version**
- Steel 11SMnPb30+C, galvanised
- Stainless steel 303



DISCOUNTS Steel

Qty	1+	10+	20+	50+
Disc.	List	-10%	-15%	On request





DISCOUNTS Stainless steel

Qty	1+	4+	10+	20+
Disc.	List	-10%	-15%	On request

Part number	ØD1 H9	ØD2	A1 B	h11	L1 +/-0,5	L2 +/-0,3	L3	L4 +/-0,2	G +/-0,5	f +/-0,2	Weight (g)	Price each 1 to 5
Steel												
CLM-4	4	M4x0,7	4	8	21	16	6	10,0	6,0	0,5	6	✓ 1,92 €
CLM-5	5	M5x0,8	5	10	26	20	8	12,5	7,5	0,5	12	✓ 1,85 €
CLM-6	6	M6x1	6	12	31	24	11	15,0	9,0	0,5	21	✓ 2,69 €
CLM-8	8	M8x1,25	8	16	42	32	14	20,0	12,0	0,5	51	✓ 3,64 €
CLM-10	10	M10x1,5	10	20	52	40	18	25,0	15,0	0,5	98	✓ 3,43 €
CLM-12	12	M12x1,75	12	24	62	48	22	30,0	18,0	0,5	168	✓ 8,05 €
CLM-16	16	M16x2	16	32	83	64	30	40,0	24,0	1,0	397	✓ 10,08 €
Stainless steel												
CLM-4/SS	4	M4x0,7	4	8	21	16	6	10,0	6,0	0,5	6	✓ 5,33 €
CLM-5/SS	5	M5x0,8	5	10	26	20	8	12,5	7,5	0,5	12	✓ 7,56 €
CLM-6/SS	6	M6x1	6	12	31	24	11	15,0	9,0	0,5	21	✓ 10,97 €
CLM-8/SS	8	M8x1,25	8	16	42	32	14	20,0	12,0	0,5	51	✓ 9,52 €
CLM-10/SS	10	M10x1,5	10	20	52	40	18	25,0	15,0	0,5	98	- 8,98 €
CLM-12/SS	12	M12x1,75	12	24	62	48	22	30,0	18,0	0,5	168	- 12,55 €
CLM-16/SS	16	M16x2	16	32	83	64	30	40,0	24,0	1,0	397	- 36,10 €

*Depending on availability - Dimensions in mm

Instruction guide



Our other products



AC156-157
Strike for toggle latch,
25.5mm



WJUM20
Drylin® W bearing
block, Slide



BABpss
301 Stainless steel
ball pin, Stainless
steel



CFF
Female rod ends DIN
ISO12240-4, Steel /
bronze



PSG05
Spur gear - precision
range, Case hardened
steel 20NCD2



LRX
Linear roller slide, Rail
- from 9410 N to
101000 N



CHT
Asynchronous AC
motor, 0.09kW



SSB
Stainless steel bevel
gear, 1:1



DCG
Suction cup, 2.5
bellows, natural
rubber



BTE
Universal tension arm,
For normal
applications



CHM63
Worm and wheel gear
reducer, up to 196
Nm



GTCS
Belt tensioner, For use
in hostile
environments

Complementary products



CLM
Male clevis end, Steel
short



COA-COG
Surface mounting
plate, Surface
mounting plate for
clevis



CLR
Straight clevis,
Straight clevis for use
with a male clevis



CNA-CNG
Right angled
mounting plate, Right
angled mounting
plate for clevis