
Centerless ground shaft

Stainless steel

GR

- ***Material: stainless steel 303***
- *Standard length from 300mm to 1000mm cf. column L*
- *External diameter tolerance: h6*
- *Straightness: 0.01/300mm*
- *Surface finish: Ra 0.4*





DISCOUNTS

Qty.	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØD	L	Stock*	Price each 1 to 5
GR2.992-6	2,992	600	✔	22,84 €
GR3.000-6	3,000	600	✔	14,36 €
GR3.992-6	3,992	600	✔	19,07 €
GR3.999-6	3,999	600	✔	28,47 €
GR4.991-9	4,991	900	✔	32,81 €
GR5.000-6	5,000	600	✔	18,01 €
GR5.993-6	5,993	600	✔	37,56 €
GR5.992-9	5,992	900	-	35,55 €
GR6.000-6	6,000	600	✔	35,55 €
GR6.000-9	6,000	900	✔	35,55 €
GR7.000-6	7,000	600	✔	27,08 €
GR7.000-9	7,000	900	-	40,48 €
GR7.993-6	7,993	600	✔	33,37 €
GR7.993-9	7,993	900	-	49,99 €
GR8.000-6	8,000	600	✔	31,67 €
GR8.992-9	8,992	900	-	89,21 €
GR9.992-9	9,992	900	✔	93,60 €

Part number	ØD	L	Stock*	Price each 1 to 5
GR9.993-10	9,993	1000	-	110,72 €
GR10.000-4	10,000	400	✔	36,25 €
GR10.000-9	10,000	900	-	92,95 €
GR10.000-10	10,000	1000	-	110,72 €
GR11.991-4	11,991	400	-	49,06 €
GR11.993-1	11,993	1000	-	144,19 €
GR12.000-4	12,000	400	✔	49,06 €
GR12.000-9	12,000	900	-	127,48 €
GR12.000-10	12,000	1000	✔	146,78 €
GR12.993-4	12,993	400	-	51,26 €
GR12.993-9	12,993	900	-	on request
GR13.993-9	13,993	900	-	149,97 €
GR14.991-9	14,991	900	-	199,41 €
GR16.000-9	16,000	900	-	199,41 €
GR19.992-9	19,992	900	✔	263,87 €
GR25.000-9	25,000	900	-	367,92 €
GR29.992-9	29,992	900	-	500,59 €

**Depending on availability - Dimensions in mm*

Our other products



Latch, Spring loaded latch - stainless steel



Worm, Hardened steel



Chain sprocket - Stainless steel, 6mm (DIN 04-1)



Fixed tube carrier, Fixing accessory Ø10 to Ø14



Ballscrew, Flanged nut - Multiple starts



Flange with bearing, Bearing secured with circlips



Accessories for PRES-3HR and PRES-4HR presses, Set of slot nuts for T



Backlash free coupling Gerwah®, from 0.5 to 35Nm



Suction cup, natural rubber



Bushing, Self-lubricating sintered bronze



Pillow block, Cast iron



,

Complementary products



Bushing, Universal polymer



Ground precision shaft, 304L stainless steel shaft