

Internal gear



Module

Steel or **machined** plastic

0,4 
1,0 

- Pressure angle 20°
- Materials:
steel 20NCD2 or
delrin plastic (machined parts)


Accessories

- Spur gears with the same module ex
G0,4..., ZG0,4..., G1, ZG1...



IN : Steel

ZIN : Delrin



DISCOUNT Steel

| | | | | |
|-------|-----------|------|------------|-----|
| Qty | 1+ | 6+ | 20+ | 40+ |
| Disc. | List -12% | -25% | On request | |

DISCOUNT Delrin

| | | | |
|-------|-----------|------------|-----|
| Qty | 1+ | 6+ | 30+ |
| Disc. | List -22% | On request | |

| Part number | | Z | PCD | Internal | | Boss | | Price each 1 to 5 | | |
|-------------------|------------|-------|-----|----------|-----|------|---|-------------------|----------|------------|
| Steel IN | Delrin ZIN | teeth | ØP | ØA | ØD | L | B | ØM | Steel IN | Delrin ZIN |
| Module 0.4 | | | | | | | | | | |
| IN0.4-100 | ZIN0.4-100 | 100 | 40 | 39,2 | 60 | 5 | 3 | 55 | 76,28 € | 54,89 € |
| IN0.4-120 | ZIN0.4-120 | 120 | 48 | 47,2 | 75 | 5 | 3 | 70 | 85,35 € | 61,31 € |
| IN0.4-150 | ZIN0.4-150 | 150 | 60 | 53,2 | 75 | 5 | 3 | 70 | 97,29 € | 69,93 € |
| IN0.4-200 | ZIN0.4-200 | 200 | 80 | 79,2 | 125 | 5 | 3 | 100 | 129,41 € | 93,06 € |
| Module 1.0 | | | | | | | | | | |
| IN1-58 | ZIN1-58 | 58 | 58 | 56 | 100 | 11 | 8 | 94 | 103,00 € | 74,18 € |
| IN1-60 | ZIN1-60 | 60 | 60 | 58 | 100 | 11 | 8 | 94 | 104,35 € | 75,09 € |
| IN1-100 | ZIN1-100 | 100 | 100 | 98 | 150 | 11 | 8 | 125 | 179,11 € | 128,91 € |

Dimensions in mm

Steel or **machined** plastic

Module



- Pressure angle 20°
- Materials:
steel 20NCD2 or
delrin plastic (machined parts)

Accessories


- Spur gears with the same module ex
G0,4..., ZG0,4...,G2, ZG2...



IN : Steel



ZIN : Delrin



DISCOUNT Steel

| | | | | |
|-------|-----------|------|------------|-----|
| Qty | 1+ | 6+ | 20+ | 40+ |
| Disc. | List -12% | -25% | On request | |

DISCOUNT Delrin

| | | | |
|-------|-----------|------------|-----|
| Qty | 1+ | 6+ | 30+ |
| Disc. | List -22% | On request | |

| Part number | | Z | PCD | Internal | | | Boss | | Price each 1 to 5 | |
|-------------------|------------|-------|-------|----------|-----|----|------|-----|-------------------|------------|
| Steel IN | Delrin ZIN | teeth | ØP | ØA | ØD | L | B | ØM | Steel IN | Delrin ZIN |
| Module 1.5 | | | | | | | | | | |
| IN1.5-41 | ZIN1.5-41 | 41 | 61,5 | 58 | 100 | 15 | 12 | 94 | 117,59 € | 84,52 € |
| IN1.5-60 | ZIN1.5-60 | 60 | 90,0 | 87 | 150 | 15 | 12 | 125 | 180,77 € | 130,03 € |
| IN1.5-100 | ZIN1.5-100 | 100 | 150,0 | 147 | 200 | 15 | 12 | 175 | 306,05 € | 235,90 € |
| Module 2.0 | | | | | | | | | | |
| IN2-40 | ZIN2-40 | 40 | 80 | 76 | 150 | 15 | 12 | 125 | 162,35 € | 113,62 € |
| IN2-60 | ZIN2-60 | 60 | 120 | 116 | 175 | 15 | 12 | 150 | 252,94 € | 177,05 € |
| IN2-80 | ZIN2-80 | 80 | 160 | 156 | 220 | 15 | 12 | 200 | 332,91 € | 233,01 € |
| IN2-100 | ZIN2-100 | 100 | 200 | 196 | 250 | 15 | 12 | 220 | 428,24 € | 299,74 € |

Dimensions in mm