


**Steel C45 or Stainless steel 316**
**KS  
KSss**

- Long key bars to be cut to the desired length
- Conform to DIN6880  
Material  
Steel C45 (Breaking strength 50kg/mm<sup>2</sup> mini)  
Stainless steel 316Ti (X6CrNiMoTi17-12-2)


**DISCOUNTS**

<b>Qty</b>	1+	6+	20+
<b>Disc.</b>	List	-15%	On request

Part number	Steel	Stainless	W (h9)	H (h11)	L (mm)	Stock*		Price each 1 to 5	
						Steel	Stainless	Steel	Stainless
KS2-500	-	-	2	2	500	-	-	5,80 €	-
KS3-500	-	-	3	3	500	-	-	5,00 €	-
KS4-500	-	-	4	4	500	-	-	6,00 €	-
KS5-500	-	KS5-500/SS	5	5	500	-	-	7,70 €	56,84 €
KS6-500	-	KS6-500/SS	6	6	500	-	-	9,85 €	58,58 €
KS8-500	-	-	8	8	500	-	-	11,44 €	-
KS87-500	-	KS87-500/SS	8	7	500	-	-	9,84 €	83,04 €
KS10-500	-	-	10	10	500	-	-	16,72 €	-
KS108-500	-	KS108-500/SS	10	8	500	-	-	14,00 €	115,99 €
KS12-500	-	-	12	12	500	-	-	21,93 €	-
KS128-500	-	KS128-500/SS	12	8	500	-	-	12,57 €	139,59 €
KS14-500	-	-	14	14	500	-	-	25,89 €	-
KS149-500	-	KS149-500/SS	14	9	500	-	-	16,50 €	189,98 €
KS1610-500	-	KS1610-500/SS	16	10	500	-	-	20,94 €	235,43 €
KS1811-500	-	KS1811-500/SS	18	11	500	-	-	25,92 €	281,48 €
KS2012-500	-	-	20	12	500	-	-	29,46 €	-
KS2214-500	-	KS2214-500/SS	22	14	500	-	-	38,19 €	423,38 €
KS2514-500	-	-	25	14	500	-	-	43,35 €	-

\*Depending on availability - Dimensions in mm

## Our other products



UFX

Uneflex® elastic coupling, range



PR40

Articulated foot Ø50, Ø 50




ADL\_F

Female eye bolt conforms to DIN582, Steel



EAR

Bearing locknut, Self locking locknut - nylon lock washer



RRP

Connecting plate for RPP type timing belts, RRP5



LPCM

Lever with cylindrical handle, Black Duroplast, steel lever



BLH20

Right angled gearbox, from 0.53 to 1.77



GET-AL

Jaw coupling, economy range, Aluminium



PGM52-M4

Pull handle, Aluminium



CHAL3

Piano hinge, Aluminium



BSM\_LOK


Long-Lok spring plunger with internal hexagonal socket,



PLC\_PLT

Magnetic stud with threaded hole, With threaded hole

## Complementary products



KS

Keysteel, Steel - Keystock



KKSS

Rounded end feather key, Stainless steel