

- Very high deformation allowing high levels of energy to be absorbed
- Progressive deformation
- Materials:
  - Core: Stainless steel plates (A2)
  - Head: Rubber
- **Hardness: NK 55-60 Shore A**
- Working temp: -40°C to +70°C

### Uses


- Shock absorbing stop

### Info.

- Not sold individually, please contact us for details
- Load and stiffness figures are given as a guide only



stainless steel



### DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc. List	-	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	Compression Stiffness (N/mm)	Max load (N)	Stock*	Price each 1 to 5
E-ZY4-10-10/SS	M4	10	10	38	43	✓	2,54 €
E-ZY4-10-15/SS	M4	10	15	-	-	✓	1,98 €
E-ZY4-15-15/SS	M4	15	15	74	95	✓	2,16 €
E-ZY6-20-15/SS	M6	20	15	138	170	✓	2,87 €
E-ZY6-20-20/SS	M6	20	20	-	-	✓	3,00 €
E-ZY6-25-10/SS	M6	25	10	-	-	✓	3,15 €
E-ZY6-25-20/SS	M6	25	20	128	280	✓	3,38 €
E-ZY6-25-30/SS	M6	25	30	80	280	✓	4,00 €
E-ZY8-30-15/SS	M8	30	15	-	-	✓	4,00 €
E-ZY8-30-17/SS	M8	30	17	-	-	✓	4,00 €
E-ZY8-30-20/SS	M8	30	20	200	400	✓	4,46 €
E-ZY8-30-30/SS	M8	30	30	120	400	✓	5,42 €
E-ZY8-40-30/SS	M8	40	30	23	234	✓	6,66 €
E-ZY10-50-20/SS	M10	50	20	680	1000	✓	8,48 €
E-ZY10-50-30/SS	M10	50	30	425	1000	✓	9,22 €
E-ZY10-50-40/SS	M10	50	40	-	-	✓	10,06 €
E-ZY10-50-50/SS	M10	50	50	-	-	✓	11,89 €
E-ZY12-75-25/SS	M12	75	25	2000	2300	-	18,20 €
E-ZY12-75-55/SS	M12	75	55	-	-	-	26,69 €

\*Depending on availability - Dimensions in mm

## Our other products



DGSI

Female rod ends,  
Steel / steel -  
Economy range



T5P\_T10P

Connecting plate for T  
type timing belts, T10



PT821

Drive sprocket for slat  
top chain, Ranges 821  
and 805




TCL

T-Clip - Aluminium  
profile attachment, T-  
Clip



INO

Internal gear, Steel  
20NC22



EM

Magnetic label,  
Flexible magnet



DGSA

Male rod ends , Steel /  
steel - Economy range



HTD8M\_30

HTD Heavy duty  
timing pulley, HTD8  
Cast



VDSQ

Sliding lock  
adjustment system,  
Sliding lock for square



AT5M AT10M

AT type timing belt  
per metre, AT10 Steel  
cored polyurethane



DOMI120


Connecting kits, XZ  
linking kit



ACLAPA

Magnetic stop for  
aluminium profile,  
Magnetic stop

## Complementary products



EZY

Cylindrical stop, Steel



DZYSS

Stainless steel  
cylindrical stop,  
stainless steel