



- The tabs around the washer fold down into the tabs on the KM locknut
- The washer being held in place in rotation by the keyway, the system guarantees absolute security
- Material: steel

Accessories

- KM locknut



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-30%	-50%	On request

Part number	For locknut	Ød	ØD	ØD2	e	f	s	Weight (g)	Stock*	Price each 1 to 9
MB3	KM3	17	32	24	4	15,5	1,00	3,1	✓	0,40 €
MB4	KM4	20	36	26	4	18,5	1,00	3,5	✓	0,40 €
MB5	KM5	25	42	32	5	23,0	1,00	6,4	✓	0,45 €
MB6	KM6	30	49	38	5	27,5	1,25	7,8	✓	0,36 €
MB7	KM7	35	57	44	6	32,5	1,25	10,4	✓	0,53 €
MB8	KM8	40	62	50	6	37,5	1,25	12,3	✓	0,67 €
MB9	KM9	45	69	56	6	42,5	1,25	15,2	✓	0,62 €
MB10	KM10	50	74	61	6	47,5	1,25	16,0	✓	1,03 €
MB11	KM11	55	81	67	8	52,5	1,25	19,6	✓	1,07 €
MB12	KM12	60	86	73	8	57,5	1,50	25,3	✓	1,25 €
MB13	KM13	65	92	79	8	62,5	1,50	29,0	✓	1,42 €
MB14	KM14	70	98	85	8	66,5	1,50	30,4	-	1,51 €
MB15	KM15	75	104	90	8	71,5	1,50	35,6	-	1,96 €
MB16	KM16	80	112	95	10	76,5	1,75	46,4	✓	2,46 €
MB17	KM17	85	119	102	10	81,5	1,75	52,4	-	2,90 €
MB18	KM18	90	126	108	10	86,5	1,75	62,3	-	3,30 €
MB19	KM19	95	133	113	10	91,5	1,75	67,0	-	3,97 €
MB20	KM20	100	142	120	12	96,5	1,75	76,5	-	5,18 €
MB22	KM22	110	154	133	12	105,5	1,75	94,0	-	6,42 €
MB24	KM24	120	164	138	14	115,0	2,00	105,0	-	8,30 €
MB26	KM26	130	175	149	14	125,0	2,00	113,0	-	9,73 €
MB28	KM28	140	192	160	15	135,0	2,00	142,0	-	12,41 €
MB30	KM30	150	205	171	15	145,0	2,00	155,0	-	15,99 €

*Depending on availability - Dimensions in mm

Our other products



Moulded plastic bevel gear (nylon), 1:1



Safety washer Hygienic Usit®, Stainless steel



Moulded plastic spur gear, Moulded plastic (nylon)



Right angled gearbox, bored shafts, up to 10.3 Nm



Articulated fixable foot with pressed base $\varnothing 100$, $\varnothing 100$



Articulated foot $\varnothing 50$, $\varnothing 50$



Spring plunger, With sensor adaptor




Manual workbench press, Force up to 400kg




Shaft for worm and wheel reducer CHMR



Spur gear - precision range, Case hardened




RPP heavy duty timing belt, RPP14



Right angled gearbox, up to 128 Nm

Complementary products



Bearing locknut, Locknut KM



Precision locknut, Precision locknut