



Bevel gear for use in food industry

Moulded blue PA6 Nylon

Ratio
2:1-3:1


- Moulded gear for use in food applications
- Pressure angle: 20°
- Material:
Blue glass-fibre reinforced Polyamide
- Two identical gears must be ordered to make a pair

Info


- *Pre-bore after de-moulding, must be machined before installation.
- We are unable to modify these products



Food industry



Ratio 2:1



Ratio 3:1

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	Net	-10%	-15%	-25%	On request

Part N°	Teeth Z	Module	ØDe	ØDp	B	F	ØM Hub	ØA* Pre-bore	dm	L	Lm	Price each. 1 to 9
Ratio 2:1												
MDB1.5-16/ALI	16	1,5	26,7	24	20,0	8	17,5	8	36,4	20,0	10,5	10,51 €
MDB1.5-32/ALI	32	1,5	49,3	48	19,5	8	33,0	12	27,5	19,5	11,5	18,02 €
MDB2-16/ALI	16	2	35,6	32	23,0	10	23,5	10	45,4	23,0	11,5	12,29 €
MDB2-32/ALI	32	2	65,8	64	25,0	12	40,5	12	35,2	25,0	10	26,85 €
MDB2.5-16/ALI	16	2,5	44,4	40	27,5	12	30,0	12	56	27,5	13,5	33,29 €
MDB2.5-32/ALI	32	2,5	82,2	80	31,0	13	50,0	15	43,5	25,5	15,5	27,71 €
MDB3-16/ALI	16	3	53,4	48	28,0	15	40,5	12	61,6	28,0	12	12,50 €
MDB3-32/ALI	32	3	98,7	96	34,5	18	61,0	16	50,4	34,5	16	56,19 €
Ratio 3:1												
MTB2.5-16/ALI	16	2,5	44,7	40	26,5	18	34,0	14	70,4	26,5	9,2	38,60 €
MTB2.5-48/ALI	48	2,5	121,6	120	31,0	18	60,0	20	44,6	25,0	16	28,29 €
MTB3-16/ALI	16	3	53,7	48	30,0	18	35,0	10	84,2	30,0	11	57,64 €
MTB3-48/ALI	48	3	145,9	144	38,0	18	50,0	20	54,1	31,0	19	57,64 €

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel


cial2@hpceurope.com

HPC

SUPPLEMENT 2019

29

Our other products



MR_MMR
Metric section rack,
Steel



BAG
Steel Clamping collar,
Steel



RTTss
Locking assembly,
Medium/high torque



PTA100
Articulated levelling
foot, pressed base
Ø100, Ø 100



COA-COG
Surface mounting
plate, Surface
mounting plate for
clevis



GLT3E-58
Telescopic drawer,



PRF-P
Aluminium profile feet
support, For feet or
casters



MDPOT
Potentiometer,



RPCtcss
Swivel castor with
central hole, Stainless
steel - Polyamide -



LVT
Miniature motorised
actuator 4A, 4 amperes



G3
Steel spur gear, Steel
20NCD2



BIMSS
Indexing plunger mini,
miniature - Stainless
steel

Complementary products



MDB_MTB
Moulded plastic bevel
gear (nylon), 2:1