


- Male/female sleeve
- Materials:
 - Galvanised steel
 - 303 Stainless steel
- Supplied by the pack



DISCOUNTS

Qty	1+	5+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	OF	OT	S	L	X	Y	Qty per pack	Price each 1 to 4
Steel								
MHX6-8-19/B	M6	M8	13	19	7	7	20	15,91 €
MHX8-6-20/B	M8	M6	13	20	8	7	20	15,91 €
MHX8-10-23/B	M8	M10	13	23	8	9	20	15,91 €
MHX8-12-23/B	M8	M12	17	23	8	8	20	22,37 €
MHX10-6-21/B	M10	M6	13	21	8	7	20	15,91 €
MHX10-8-21/B	M10	M8	13	21	8	7	20	15,91 €
MHX10-12-25/B	M10	M12	17	25	10	8	20	22,37 €
MHX10-16-32/B	M10	M16	24	32	10	13	20	57,85 €
MHX12-8-23/B	M12	M8	13	23	10	7	20	15,91 €
MHX12-10-23/B	M12	M10	13	23	10	8	20	15,91 €
MHX12-16-32/B	M12	M16	24	32	10	13	20	57,85 €
MHX16-10-32/B	M16	M10	19	32	14	9	20	34,71 €
MHX16-12-32/B	M16	M12	19	32	14	10	20	34,71 €
Stainless steel								
MHX6-8-19/SS/B	M6	M8	13	19	7	7	20	67,94 €
MHX8-6-20/SS/B	M8	M6	13	20	8	7	20	67,94 €
MHX8-10-23/SS/B	M8	M10	13	23	8	9	20	67,94 €
MHX8-12-23/SS/B	M8	M12	17	23	8	8	20	87,92 €
MHX10-6-21/SS/B	M10	M6	13	21	8	7	20	67,94 €
MHX10-8-21/SS/B	M10	M8	13	21	8	7	20	67,94 €
MHX10-12-25/SS/B	M10	M12	17	25	10	8	20	87,92 €
MHX10-16-32/SS/B	M10	M16	24	32	10	13	20	142,29 €
MHX12-8-23/SS/B	M12	M8	13	23	10	7	20	67,94 €
MHX12-10-23/SS/B	M12	M10	13	23	10	8	20	67,94 €
MHX12-16-32/SS/B	M12	M16	24	32	10	13	20	142,29 €
MHX16-10-32/SS/B	M16	M10	19	32	14	9	20	100,82 €
MHX16-12-32/SS/B	M16	M12	19	32	14	10	20	100,82 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Our other products



CHAR

Spring hinges,
screwed



BAG0

Shaft collar, Stainless
steel



ACLERP

Roller block, With
guide rail



KB_OP

Linear bearing,
Precision - steel



PT821

Drive sprocket,
Ranges 821 and 805




VMS

Stainless steel set
screw, Knurled



LVT

Miniature motorised
actuator, 4 amperes



MRS

Rack, square section,
Stainless steel



PRF_P

Floor anchor, Anchor
foot



DB_ECO

Bevel gear - Steel
C43, 2:1



BABA

Lifting ring, Steel



FS

Bearing - accessories,
Spring washer

Complementary products



TIFbout

Threaded stud - DIN
976A, Steel



MHX

Threaded sleeves,
Hexagonal - steel



MCL

Threaded sleeves,
Cylindrical - steel



MCLred

Reducing sleeve,
Cylindrical - steel