

Low cost quick link



MRAECO

Link diameter 3.5-16mm

- For joining or closing chains
- White chromed steel
- Low cost range, no SWL specified
- Engraved with ring diameter




Economy range

Application

- Nominal load figures are given as an indication only
- Should not be used for lifting (load values not guaranteed)

Info

- Also available in stainless steel



DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	A	B	C	E	Nominal load (kg)	Weight (g)	Stock*	Price each
									1 to 19
MRA1-03/ECO	3,5	36,0	10,0	5,0	12,0	100	8	✓	0,49 €
MRA1-04/ECO	4,0	39,5	11,5	6,0	14,0	180	12	✓	0,60 €
MRA1-05/ECO	5,0	49,5	13,0	7,0	17,0	280	22	-	0,66 €
MRA1-06/ECO	6,0	57,0	14,5	8,0	20,0	400	36	✓	0,82 €
MRA1-07/ECO	7,0	66,0	16,0	9,0	22,5	550	52	-	1,10 €
MRA1-08/ECO	8,0	74,0	17,5	10,0	24,0	700	76	✓	1,28 €
MRA1-09/ECO	9,0	80,0	19,0	11,0	27,0	900	110	-	1,78 €
MRA1-10/ECO	10,0	89,0	20,5	12,0	30,0	1100	146	✓	2,37 €
MRA1-12/ECO	12,0	104,5	23,5	14,0	34,0	1500	234	-	3,64 €
MRA1-14/ECO	14,0	121,0	26,5	17,0	39,0	2200	358	-	7,25 €
MRA1-16/ECO	16,0	140,0	29,5	19,0	43,0	2900	520	-	11,78 €

*Depending on availability - Dimensions in mm

Our other products




SH1

Parallel axis helical gear, Machined plastic (delrin)



CF

Cam follower, Standard - steel



CHB

Worm and wheel gear reducer, up to 41 Nm




AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane




UCFL_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



RPP

Connecting plate for RPP type timing belts, RPPB



QNJ

Single row cylindrical roller bearing, Single flange on inner ring



DOMI30

Accessories, Plate



RNAST

Cam follower without axial guide, Without




BSM_LOK

Long-Lok spring plunger with internal



ZG2

Plastic spur gear, Machined plastic



PF40NM

Worm and wheel gear reducer, up to 18 Nm

Complementary products



MRA

Quick link, Steel



MRA_SS

Stainless steel Quick link, Stainless steel



MRASeco

Low cost stainless steel quick link, Stainless steel



CHN_CHNSS

Straight long link chain, Galvanised steel