

# Set screw **Delrin tip**

Ste

NTM<sub>DL</sub>

Blackened steel finish

**- Materiel**

Screw : steel (class 10.9)


Tip : Delrin

**Info**

- The tip is fitted into the screw.  
These screws are designed to lock or gently hold screws, axles, shafts or other components with a high quality surface finish.



Delrin tip




**INCREASED STOCK**

**DISCOUNTS**

Qty	1+	6+	30+	40+	60+	100+	300+
Disc.	List	-10%	-15%	-20%	-25%	-45%	On request

Part number	ØD	ØD1	L	SW	Stock*	Price each 1 to 19
NTM4-7/DL	M4	2	7	2	✓	2,98 €
NTM4-9/DL	M4	2	9	2	✓	2,98 €
NTM4-11/DL	M4	2	11	2	✓	2,98 €
NTM4-13/DL	M4	2	13	2	✓	2,98 €
NTM4-17/DL	M4	2	17	2	✓	2,98 €
NTM4-31/DL	M4	2	31	2	✓	7,21 €
NTM4-41/DL	M4	2	41	2	-	7,37 €
NTM5-9/DL	M5	3	9	2,5	✓	2,75 €
NTM5-11/DL	M5	3	11	2,5	-	2,75 €
NTM5-13/DL	M5	3	13	2,5	-	2,75 €
NTM5-17/DL	M5	3	17	2,5	✓	2,75 €
NTM5-21/DL	M5	3	21	2,5	-	2,98 €
NTM5-31/DL	M5	3	31	2,5	-	7,75 €
NTM5-41/DL	M5	3	41	2,5	-	7,87 €

\*Depending on availability - Dimensions in mm



**INCREASED STOCK**

*soft contact*

Part number	ØD	ØD1	L	SW	Stock*	Price each 1 to 19
NTM6-11/DL	M6	3,5	11,3	3	✓	2,75 €
NTM6-13/DL	M6	3,5	13,3	3	-	2,75 €
NTM6-17/DL	M6	3,5	17,3	3	✓	2,98 €
NTM6-21/DL	M6	3,5	21,3	3	✓	2,98 €
NTM6-26/DL	M6	3,5	26,3	3	✓	3,14 €
NTM6-41/DL	M6	3,5	41,3	3	✓	7,93 €
NTM6-51/DL	M6	3,5	51,3	3	✓	8,08 €
NTM6-61/DL	M6	3,5	61,3	3	-	8,14 €
NTM8-13/DL	M8	5	13,6	4	-	3,14 €
NTM8-17/DL	M8	5	17,6	4	✓	3,14 €
NTM8-21/DL	M8	5	21,6	4	-	3,19 €
NTM8-26/DL	M8	5	26,6	4	✓	3,42 €
NTM8-33/DL	M8	5	33,6	4	✓	3,87 €
NTM8-51/DL	M8	5	51,6	4	-	7,75 €
NTM8-61/DL	M8	5	61,6	4	-	7,87 €
NTM8-81/DL	M8	5	81,6	4	-	7,93 €
NTM10-18/DL	M10	6,5	17,9	5	✓	3,75 €
NTM10-22/DL	M10	6,5	21,9	5	-	3,87 €
NTM10-27/DL	M10	6,5	26,9	5	-	3,93 €
NTM10-34/DL	M10	6,5	33,9	5	✓	4,54 €
NTM10-42/DL	M10	6,5	41,9	5	-	5,20 €
NTM10-52/DL	M10	6,5	51,9	5	-	7,87 €
NTM10-62/DL	M10	6,5	61,9	5	-	7,98 €
NTM10-82/DL	M10	6,5	81,9	5	✓	8,08 €
NTM12-22/DL	M12	8	22,1	6	-	4,36 €
NTM12-27/DL	M12	8	27,1	6	-	4,54 €
NTM12-34/DL	M12	8	34,1	6	-	4,93 €
NTM12-42/DL	M12	8	42,1	6	-	5,54 €
NTM12-52/DL	M12	8	52,1	6	-	6,36 €
NTM12-62/DL	M12	8	62,1	6	-	8,14 €
NTM12-82/DL	M12	8	82,1	6	-	8,31 €

\*Depending on availability - Dimensions in mm

## Our other products



HS

Hexagonal spacer,  
Stainless steel 303



UTKswcr

Utilitrak® 3 wheels  
carriage, Steel roller  
carriage



GALRUB

60mm rubber wheel  
for conveyor belt,  
Rubber



MEF

Cylindrical sintered  
ferrous bush, Self-  
lubricating FP20  
ferrous all...



BOX-CS

Hose clamp, Box set  
of steel hose clamps



PR40

Articulated foot Ø40,  
Ø 40



LVT

Miniature motorised  
actuator 4A, 4 ampers




CHAPAM

Weld-on hinge with  
flat end, Steel



PVL

Small lobed handle,  
Polyamide



KGS

Ball screw, supplied by  
the metre, Rolled



NPCR

Adjustable cell  
support, Adjustable



P20

Worm and wheel gear  
reducer, up to 5 Nm

## Complementary products



NTMbr

Set screw brass tip,  
Brass-point



NTM

Nylon tipped set  
screw, Nylon-point