




- Hand brushes are used for manual cleaning, scouring, dust removal, stripping, descaling, honing or deburring operations on cylindrical surfaces: inside tubes, bottles, pin holes, rivet holes, tapped holes, secant holes, etc.
- These brushes can be used in a wide range of industries: mechanical (machine tools, maintenance), food processing, pharmaceutical and medical.

In practice

- Scrub the walls of the element to be cleaned using a rotating and back-and-forth motion.

Advice

- To prevent the bristles of the brush from twisting, we recommend that you choose one that the diameter is 10 to 15% larger than the diameter of the hole you wish to clean.



It's the end of the brush that works, not the edge.
It needs room to stand up straight

Deburring and stripping stainless steel

GPLSS



- **Stainless steel deburring brushes**

- Materials:

- Twisted galvanised steel
- Stainless steel covering

Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Deburring a gear bore

DISCOUNTS

Qty	1+	10+	25+	50+
Disc. List		-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Overall length L2	Stock*	Price each 1 to 9
GPL5-100/SS	5	100	300	✓	12,23 €
GPL8-100/SS	8	100	300	✓	10,46 €
GPL10-100/SS	10	100	300	✓	9,55 €
GPL12-100/SS	12	100	300	✓	9,55 €
GPL15-100/SS	15	100	300	✓	9,67 €
GPL20-100/SS	20	100	300	✓	10,70 €
GPL25-100/SS	25	100	300	✓	10,11 €

*Depending on availability - Dimensions in mm

- Deburring and cleaning brush for all materials



- Materials:

- Twisted galvanised steel
- Galvanized steel twist
- Steel covering



Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Stripping of a pulley bore

DISCOUNTS

Qty	1+	10+	25+	50+
Disc. List	-5%	-10%	On request	

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/AC	5	100	300	✓	12,42 €
GPL8-100/AC	8	100	300	-	8,07 €
GPL10-100/AC	10	100	300	✓	8,07 €
GPL12-100/AC	12	100	300	-	8,22 €
GPL15-100/AC	15	100	300	-	8,53 €
GPL20-100/AC	20	100	300	-	10,08 €
GPL25-100/AC	25	100	300	-	10,08 €

*Depending on availability - Dimensions in mm

For deburring and stripping softer materials

GPL_{BR}




- Deburring and stripping brushes for aluminium, bronze and brass

- Materials:

- Twisted galvanised steel
- Brass covering

Applications

- Deburring of pin holes, rivet holes, tapped holes, intersecting holes
- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas
- Removing rust
- Cleaning
- Stripping



Deburring a trapezoidal nut

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL5-100/BR	5	100	300	✓	12,23 €
GPL8-100/BR	8	100	300	-	10,24 €
GPL10-100/BR	10	100	300	-	9,22 €
GPL12-100/BR	12	100	300	✓	9,28 €
GPL15-100/BR	15	100	300	✓	9,28 €
GPL20-100/BR	20	100	300	✓	9,84 €
GPL25-100/BR	25	100	300	✓	9,84 €

*Depending on availability - Dimensions in mm




- Deburring brushes for soft materials

- Materials:

- Twisted galvanised steel
- Nylon covered

Applications

- Gentle cleaning of hollow containers (tubes, bottles, holes)
- Gentle cleaning of hard-to-reach areas



Cleaning the cooling fins of a gearbox

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL4-100/NY	4	100	300	✓	7,76 €
GPL6-100/NY	6	100	300	✓	5,11 €
GPL8-100/NY	8	100	300	✓	5,14 €
GPL10-100/NY	10	100	300	✓	5,18 €
GPL12-100/NY	12	100	300	✓	5,21 €
GPL15-100/NY	15	100	300	✓	5,27 €
GPL20-100/NY	20	100	300	✓	5,32 €
GPL25-100/NY	25	100	300	✓	5,41 €
GPL30-100/NY	30	100	300	✓	5,59 €
GPL40-100/NY	40	100	300	✓	5,79 €

*Depending on availability - Dimensions in mm

- Brushes for the cleaning and removal of dust

- Materials:




Twisted galvanised steel
Hog bristle silk covering

Application

- Cleaning of hollow containers (tubes, bottles, holes)
- Cleaning of hard-to-reach areas

Advantage

- Anti-static



Cleaning of hard-to-reach areas


DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL15-100/SO	15	80	300	✓	8,53 €
GPL20-100/SO	20	80	300	-	10,08 €
GPL25-100/SO	25	80	300	✓	8,99 €

*Depending on availability - Dimensions in mm

Our other products



T0

Torsion spring,
Stainless steel



DOMI120

Accessories, Clamping
lever



PCS6ECO

Chain sprocket - steel,
6mm (DIN 04-1)



VELprf

Clip-on base for hook-
and-loop strip,
Polyamide



DIL

Lever operated
locking bolt, lever
clamp



DFG

Flat suction cup,
silicon



BTC20_10

End cap for
rectangular tube,
Standard



DKN

Bellows coupling
Gerwah®, from 0.4 to
10Nm



GAL48_OMNI

Omni-directional
roller, Omni-
directional



RBGtc

Swivel castor with
central hole, Steel -
grey rubber



VTLB


Three-lobed knob,
Thermoplastic / Brass
or stainless steel



SCE_SS


Stainless steel U-
shaped clamp,
Stainless steel

Complementary products



GPLss

Brush, stainless steel




GPLac

Brush, steel



GPLbr

Brush, brass



GPLso

Brush, silk