

# INDEX bolt with T handle

PITA  
PITB

Steel - thermoplastic



**- Indexing bolt with T-handle**

- The T-handle allows a good grip for easy clamping with low effort.


- Materials:

Burnished steel, class 5.8

T-handle : thermoplastic dark grey  
RAL7021 or signal red RAL3020



Shape A



Shape B

## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Colour	A	B	ØD	ØD1	L	L1	L2	L3	H	SW1	Spring force (N)		Price each 1 to 5
												Initial F1	Final F2	
<b>Shape A - No nut</b>														
PITA12-50/G	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,22 €
PITA16-60/G	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	11,88 €
PITA19-20/G	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	17,24 €
PITA12-50/R	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,22 €
PITA16-60/R	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	11,88 €
PITA19-20/R	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	17,24 €
<b>Shape B - With nut</b>														
PITB12-50/G	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,51 €
PITB16-60/G	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	12,68 €
PITB19-20/G	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	18,09 €
PITB12-50/R	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,51 €
PITB16-60/R	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	12,68 €
PITB19-20/R	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	18,08 €

Dimensions in mm

## Our other products



WJUM20

Drylin® W bearing block, Slide



PRF\_ART

Articulated bracket for use with aluminium profile, Standard



ACLBT5

Spherical ended stop for aluminium profile, Spherical ended stop



PSG25

Spur gear - precision range, Stainless steel 316



RPCplss

Swivel castor with plate, Stainless steel - Polyamide



CHM40-MOT

Asynchronous AC motorgearboxes 0.18 to 0.55kW, 0.18 to 0.55kW



BZY\_SS

Stainless steel cylindrical elastomount, Stainless steel




MHX

Hexagonal threaded sleeve, Hexagonal - stainless steel



SSHBRA

Stainless steel bevel gear, 1,5:1 2:1 3:1



CHN\_CHNSS

Straight long link stainless steel chain,



CHASb89

Hinge without pin, Plastic hinge



M1

Worm and wheel set, Bronze

## Complementary products



SLBE

Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts



PITAss

Locking bolt, with T handle



DIL

Lever operated locking bolt, lever clamp



DIA

Ring operated locking bolt, with ring