


INDEX bolt with T handle

PITA
PITB


Steel - thermoplastic

- **Indexing bolt with T-handle**
- The T-handle allows a good grip for easy clamping with low effort.
- **Materials:**
Burnished steel, class 5.8
T-handle : thermoplastic dark grey
RAL7021 or signal red RAL3020




Grey version

Red version



Shape A



Shape B

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Colour	A	B	ØD	ØD1	L	L1	L2	L3	H	SW1	Spring force (N)		Price each 1 to 5
												Initial F1	Final F2	
Shape A - No nut														
PITA12-50/G	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,22 €
PITA16-60/G	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	11,88 €
PITA19-20/G	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	17,24 €
PITA12-50/R	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,22 €
PITA16-60/R	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	11,88 €
PITA19-20/R	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	17,24 €
Shape B - With nut														
PITB12-50/G	Grey	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,51 €
PITB16-60/G	Grey	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	12,68 €
PITB19-20/G	Grey	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	18,09 €
PITB12-50/R	Red	50	15,5	6	M12x1,5	58	20	8	17	6	14	6	14	9,51 €
PITB16-60/R	Red	60	18,0	8	M16x1,5	77	26	10	23	8	19	15	35	12,68 €
PITB19-20/R	Red	72	19,0	10	M20x1,5	84	28	12	25	10	22	15	34	18,08 €

Dimensions in mm

Our other products



HW_HT
Half-rail guide, Wheel



PSG125HC
Skive hobbed spur gears - precision range, Case hardened steel 20NC2



SCA
Flat cable clamp, Steel



PRF-SMA
Closing system for aluminium profile, Easily adjustable lock



AFSE
Locking pin with interlocking safety latch, with interlocking safety...



DFG
Flat suction cup, silicon



PMC48_M8
Anti-vibration machine mount, Oval base plate



BH01
Single housed bearing, Bearing fitted with adhesive



RHTplss
High Temperature Castor, up to 200kg



SLB
Indexing plunger, stainless steel



CHASb63
Hinge without pin, Polymer pin hinge



F7-SF-SM
Multifunction display, Mounting bracket for front mounting

Complementary products



SLBE
Indexing plunger - Spacer, Spacer for SLB and SLBS index bolts



PITAss
Locking bolt, with T handle



DIL
Lever operated locking bolt, lever clamp



DIA
Ring operated locking bolt, with ring