

Spoked handwheel with revolving handle

HLUT

Aluminium


- Handwheel with revolving handle
- Materials:
 - Wheel: aluminium
 - Handle: aluminium with steel axle
- Finish: edges machined and polished
- Keyway conforms to DIN6885-1

Advantages

- Light

Options

- Handwheel without handle HLU



DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request

Part number		Revolving handle	ØD2		B3		T	Stock*		Price each 1 to 5		
With keyway	Without keyway		ØD1 (H7)	ØD3	L1	L3 (P9)		With keyway	Without keyway	With keyway	Without keyway	
Avec 3 bras												
HLUT80-10K	HLUT80-10	Ø16xM6x54,5	80	10	24	16	29	3	11,4	✓	-	37,56 € 34,76 €
HLUT100-10K	HLUT100-10	Ø16xM6x54,5	100	10	26	17	33	3	11,4	✓	-	40,03 € 36,11 €
HLUT125-12K	HLUT125-12	Ø20xM8x67,0	125	12	28	18	36	4	13,8	✓	-	48,23 € 43,88 €
HLUT140-14K	HLUT140-14	Ø20xM8x67,0	140	14	30	19	39	5	16,3	✓	-	53,81 € 49,23 €
HLUT160-14K	HLUT160-14	Ø25xM10x83,0	160	14	32	20	40	5	16,3	✓	✓	63,01 € 59,75 €
HLUT180-16K	HLUT180-16	Ø25xM10x83,0	180	16	35	22	43	5	18,3	✓	✓	72,69 € 69,33 €
HLUT200-18K	HLUT200-18	Ø25xM10x83,0	200	18	38	24	45	6	20,8	✓	✓	81,57 € 77,57 €
Avec 5 bras												
HLUT250-22K	HLUT250-22	Ø32xM12x105,5	250	22	45	28	50	6	24,8	-	✓	122,40 € 117,86 €
HLUT315-26K	HLUT315-26	Ø32xM12x105,5	315	26	53	33	56	8	29,3	-	-	167,04 € 162,35 €
HLUT400-30K	HLUT400-30	Ø36xM16x117,0	400	30	65	38	63	8	33,3	-	-	276,20 € 270,91 €
HLUT500-34K	HLUT500-34	Ø36xM16x117,0	500	34	78	45	72	10	37,3	-	-	431,03 € 420,47 €

*Depending on availability - Dimensions in mm

Our other products



PLM-C

Cylindrical holding magnets, Cylindrical holding magnet



CHA138

Screwed hinge with threaded insert, 138 degrees



GLT3E-50

Telescopic drawer,



RGS

Rotex® GS backlash free jaw coupling, from 0.5 to 190Nm



HLU

Spoked handwheel without handle, Aluminium



FHCSS

Countersunk screw, Stainless steel A2 - DIN 7991



FF15

Offset spur gear reducer, from 2.20 to 10 Nm



CHAE4080PA

Symmetrical decorative screwed hinge, Polyamide



T5P_T10P

Connecting plate for T type timing belts, T5



CHB

Worm and wheel gear reducer, up to 41 Nm



UTKswcr

Utilitrac® 3 wheels carriage, Steel roller carriage



ESCON

Speed controller 5A accessories, Kit of 4 cables for DC motor

Complementary products



HLU

Spoked handwheel without handle, Aluminium



HLUsS

Spoked handwheel, Stainless steel 316