


Cylindrical spacer



PLS

Stainless steel 303

- Machined pillar, female/female
- Material:
Stainless steel 303
- Sold by the packet



DISCOUNTS

No pack	1+	5+	20+	100+
Disc	List	-20%	-30%	On request

Part number	Nominal ØA	ØA	ØD	L	Qty. per packet	Stock*	Price per packet
PLS3-5/B	3	3,2	6	5	20	✓	26,45 €
PLS3-6/B	3	3,2	6	6	20	✓	27,88 €
PLS3-8/B	3	3,2	6	8	20	✓	28,94 €
PLS3-10/B	3	3,2	6	10	20	✓	30,88 €
PLS3-12/B	3	3,2	6	12	20	✓	31,58 €
PLS3-18/B	3	3,2	6	18	20	-	34,97 €
PLS3-25/B	3	3,2	6	25	20	-	39,03 €
PLS4-5/B	4	4,3	8	5	20	✓	28,94 €
PLS4-6/B	4	4,3	8	6	20	✓	30,52 €
PLS4-8/B	4	4,3	8	8	20	✓	31,77 €
PLS4-10/B	4	4,3	8	10	20	✓	33,84 €
PLS4-12/B	4	4,3	8	12	20	✓	34,63 €
PLS4-15/B	4	4,3	8	15	20	-	36,61 €
PLS4-20/B	4	4,3	8	20	20	-	39,18 €
PLS4-25/B	4	4,3	8	25	20	✓	42,77 €
PLS4-30/B	4	4,3	8	30	20	✓	45,75 €

*Depending on availability - Dimensions in mm

Our other products



LRR-53
Spring loaded latch,
Spring return latch -
stainless steel



ZDB
Machined plastic
bevel gear , 2:1



PPG
Indexing plunger with
flange, With
horizontal mounting
flange



GG1
Ground spur gear,
Heat treated steel



BPM-Z
Plastic slotted spring
plunger with ball tip,
Plastic body +
plastic...



PO
Pull handle - Multi-
sector, Smooth hole



RJUM05
Drylin R® linear
bearing housing,
Closed - Long



RAGFLOWsupport
Floway2® Roller track
accessory, Roller
track support



BLM
Spring loaded plunger
with ball tip, Plastic
body



AT5P_AT10P
Connecting plate for
AT type timing belts,
AT5



RCX-6
Spherical tilt washer -
DIN6319, convex



PAP
Handle for aluminium
profile, Ergonomic
handle

Complementary products



PLN
Cylindrical spacer,
Thermoplastic



PLB
Cylindrical spacer,
Brass