

Multi-sector enclosure/door handle

PO

Back to back mounting

- Ideal for back mounting, i.e. a PO handle used on one side with a PO-M handle on the other (see typical application)

- Colour: matt black

- Materials:

Handle: Fibreglass reinforced Technopolymer

Insert: Brass (PO-M version)

- PO version has a smooth bored hole for socket head screw

- PO-M has a blind threaded insert



PO version



PO-M version



Black



Red: safety

Add: /R
to end of part N°



Orange:

furniture, kitchens

Add: /O
to end of part N°




Grey: food industry

Add: /G
to end of part N°




White: medical


Add: /W
to end of part N°



PO handle



PO-M handle



Back to back mounting

DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+
Disc.	List	-5%	-10%	-15%	-20%	On request


Part number	B	A	E	F	C	G	H	ØD	Ød	Stock*	Price each 1 to 5
With smooth hole											
PO93-6	93,5	112	21	36	30	6	7	10,5	6,5	✓	3,69 €
PO117-6	117	139	26	41	34	6	9	10,5	6,5	✓	4,01 €
PO117-8	117	139	26	41	34	6	9	13,0	8,5	✓	4,01 €
PO132-6	132	156	27	45	37	9	7	10,5	6,5	✓	5,47 €
PO132-8	132	156	27	45	37	7	9	13,0	8,5	✓	8,02 €
PO179-8	179	204	28	50	42	8	9	13,0	8,5	✓	8,02 €
With threaded hole											
PO93-M5	93,5	112	21	36	30	-	9	M5	-		5,35 €
PO93-M6	93,5	112	21	36	30	-	9	M6	-	✓	5,63 €
PO117-M6	117	139	26	41	34	-	9	M6	-	✓	5,93 €
PO117-M8	117	139	26	41	34	-	9	M8	-	✓	5,93 €
PO132-M6	132	156	27	45	37	-	9	M6	-	✓	6,61 €
PO132-M8	132	156	27	45	37	-	9	M8	-	✓	6,61 €
PO179-M8	179	204	28	50	42	-	9	M8	-	✓	9,57 €

*Depending on availability - Dimensions in mm

Our other products



PSG15
Spur gear - precision range, Pre-hardened Steel 35NCD6




BMF
Knurled knob - female, Knurled - through threaded



MSP3815
Masterplate® glueable insert rectangular, rectangular with nut




NCT
Square tube connector, Fixed angle



T0
Torsion spring, Stainless steel



RJUM05
Drylin R® linear bearing housing, Closed - Long



M0
Worm and wheel set, Bronze



BSM
Spring plunger with internal hexagonal socket, steel body and pin



RFV40
Stainless steel worm and wheel gearbox,



PM3
Worm and wheel set, Non hardened steel



BFA
Shaft locking washer, E clip



PRF4590_E
Bracket for aluminium profile, PRF4590

Complementary products



PO
Pull handle - Multi-sector, Tapped recessed insert



CHC
Socket headed screw, Steel class 12.19



PCatherm
Pull handle, Thermoplastic



PENC
Recessed handle, clip-in