

Internal gear



Module


Steel or **machined** plastic

0,4 
1,0 

- Pressure angle 20°
- Materials:
steel 20NCD2 or
delrin plastic (machined parts)


Accessories

- Spur gears with the same module ex
G0,4..., ZG0,4..., G1, ZG1...



IN : Steel

ZIN : Delrin



DISCOUNT Steel

| | | | | |
|-------|-----------|------|------------|-----|
| Qty | 1+ | 6+ | 20+ | 40+ |
| Disc. | List -12% | -25% | On request | |

DISCOUNT Delrin

| | | | |
|-------|-----------|------------|-----|
| Qty | 1+ | 6+ | 30+ |
| Disc. | List -22% | On request | |

| Part number | | Z | PCD | Internal | | Boss | | Price each 1 to 5 | | |
|-------------------|------------|-------|-----|----------|-----|------|---|-------------------|----------|------------|
| Steel IN | Delrin ZIN | teeth | ØP | ØA | ØD | L | B | ØM | Steel IN | Delrin ZIN |
| Module 0.4 | | | | | | | | | | |
| IN0.4-100 | ZIN0.4-100 | 100 | 40 | 39,2 | 60 | 5 | 3 | 55 | 56,26 € | 40,49 € |
| IN0.4-120 | ZIN0.4-120 | 120 | 48 | 47,2 | 75 | 5 | 3 | 70 | 62,95 € | 45,22 € |
| IN0.4-150 | ZIN0.4-150 | 150 | 60 | 53,2 | 75 | 5 | 3 | 70 | 71,75 € | 51,58 € |
| IN0.4-200 | ZIN0.4-200 | 200 | 80 | 79,2 | 125 | 5 | 3 | 100 | 95,45 € | 68,64 € |
| Module 1.0 | | | | | | | | | | |
| IN1-58 | ZIN1-58 | 58 | 58 | 56 | 100 | 11 | 8 | 94 | 75,97 € | 54,71 € |
| IN1-60 | ZIN1-60 | 60 | 60 | 58 | 100 | 11 | 8 | 94 | 76,97 € | 55,39 € |
| IN1-100 | ZIN1-100 | 100 | 100 | 98 | 150 | 11 | 8 | 125 | 132,10 € | 95,08 € |

Dimensions in mm

Our other products



MRA_SS

Stainless steel Quick link, Stainless steel



PSG35

Spur gear - precision range, Stainless steel 316



SH1

Parallel axis helical gear, Machined plastic (delrin)



HBM

Adjustment bushing for half-rail guide, Adjustment bushing



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW




HTD8M_50

HTD Heavy duty timing pulley, HTD8 Steel



NJM

Multiple junction clamp, Multiple



T0

Torsion spring, Stainless steel



PTA150

Articulated levelling foot, pressed base Ø150, Ø 150



HBM

Adjustment bushing for half-rail guide, Adjustment bushing



ACM_AZ

Mounting bracket for bonnet fastener, Hook



BIMSS

Indexing plunger mini, miniature - Stainless steel

Complementary products



INO

Internal gear, Steel 20NCD2



ZG0

Plastic spur gear, Machined plastic (delrin)