

Indexing pin for sheet metal

Stock

PPD

For thin sheets or walls

- With or without possibility to lock in open position

- Material:

Polyamide knurled knob,

matt surface finish

Body: Chromed steel


Pin: stainless steel

Position of thin wall




Info.

- Locking version: pull and turn to lock.



Typical application:
locking



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Ød1	Ød2	L	H	L1	L2	ØD	Y	Y1	P	Weight	Stock*	Price each
											(g)	1 to 5	
Non-locking													
PPD6-8	26	6	9	23	8,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	27,26 €
PPD6-10	26	6	9	23	10,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	27,26 €
PPD8-10	32	8	8	28	10,0	7,5	12x1,5	16	18	from 1 to 5	62	-	29,98 €
PPD8-12	32	8	8	28	12,0	7,5	12x1,5	16	18	from 1 to 5	65	-	29,98 €
Locking													
PPD6-8/A	26	6	9	23	8,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	27,26 €
PPD6-10/A	26	6	9	23	10,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	27,26 €
PPD8-10/A	32	8	10	28	10,0	7,5	12x1,5	16	18	from 1 to 5	62	-	29,98 €
PPD8-12/A	32	8	10	28	12,0	7,5	12x1,5	16	18	from 1 to 5	65	✓	29,98 €

*Depending on availability - Dimensions in mm


- With or without possibility to lock in open position
- Material:
Polyamide knurled head with matt finish
Flange: Plated steel
Pin: Stainless steel

Info.

- Locking version: pull and turn to lock



Pull button to release



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Ød1	Ød2	L	H	L3	ØD	L2	A	B	C	Ød3	Weight (g)	Stock*	Price each 1 to 5
Non-locking														
PPF6-6	26	6	5	23	6	10	2	16	42	30	4,30	40,9	✓	43,40 €
PPF6-14	26	6	5	23	14	10	2	16	42	30	4,30	41,9	✓	43,40 €
PPF8-8	32	8	6	28	8	12	2	20	50	34	5,30	71,4	-	47,79 €
PPF8-18	32	8	6	28	18	12	2	20	50	34	5,30	74,4	✓	47,79 €
Locking														
PPF6-6/A	26	6	5	23	6	10	2	16	42	30	4,30	40,9	✓	41,70 €
PPF6-14/A	26	6	5	23	14	10	2	16	42	30	4,30	42,9	✓	41,70 €
PPF8-8/A	32	8	6	28	8	12	2	20	50	34	5,30	72,4	-	45,89 €
PPF8-18/A	32	8	6	28	18	12	2	20	50	34	5,30	73,4	✓	45,89 €

* Depending on availability - Dimensions in mm