

Steel C45 or Stainless steel 316
**KS
KSss**

- Long key bars to be cut to the desired length

- Conform to DIN6880


Material

Steel C45 (Breaking strength

50kg/mm² mini)

Stainless steel 316Ti

(X6CrNiMoTi17-12-2)



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-15%	On request

Part number	W	H	L	Stock*		Price each 1 to 5		
				Steel	Stainless	Steel	Stainless	
Steel	Stainless	(h9)	(h11)	(mm)				
KS2-500	-	2	2	500	-	-	5,80 €	-
KS3-500	-	3	3	500	-	-	5,00 €	-
KS4-500	-	4	4	500	-	-	6,00 €	-
KS5-500	KS5-500/SS	5	5	500	-	-	7,70 €	56,84 €
KS6-500	KS6-500/SS	6	6	500	-	-	9,85 €	58,58 €
KS8-500	-	8	8	500	-	-	11,44 €	-
KS87-500	KS87-500/SS	8	7	500	-	-	9,84 €	83,04 €
KS10-500	-	10	10	500	-	-	16,72 €	-
KS108-500	KS108-500/SS	10	8	500	-	-	14,00 €	115,99 €
KS12-500	-	12	12	500	-	-	21,93 €	-
KS128-500	KS128-500/SS	12	8	500	-	-	12,57 €	139,59 €
KS14-500	-	14	14	500	-	-	25,89 €	-
KS149-500	KS149-500/SS	14	9	500	-	-	16,50 €	189,98 €
KS1610-500	KS1610-500/SS	16	10	500	-	-	20,94 €	235,43 €
KS1811-500	KS1811-500/SS	18	11	500	-	-	25,92 €	281,48 €
KS2012-500	-	20	12	500	-	-	29,46 €	-
KS2214-500	KS2214-500/SS	22	14	500	-	-	38,19 €	423,38 €
KS2514-500	-	25	14	500	-	-	43,35 €	-

*Depending on availability - Dimensions in mm

Our other products



TC1rp
Automatic chain tensioner, With 180° guide



S4
Chain sprocket- stainless steel, 4mm



CHMX_CHMDX
Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...



SDG
Adjustable guide support bracket, Plastic



NAST
Cam follower without axial guide, With interior ring



CHAR7520
Spring hinge, screwed



UTKswrr
V shaped channel UtiliTrak®, V rail



T10-BAR
T type tooth bar stock, T10



AT5M AT10M
AT type timing belt per metre, AT5 Steel cored polyurethane



PSG25
Spur gear - precision range, Stainless steel 303



ZBconique
Machined plastic bevel gear, 1:1




ACLCHARJ
Hinge for aluminium profile, Adjusts in 2 directions

Complementary products



KK
Rounded end feather key, Steel



KS
Keysteel, Stainless steel - Keystock