

Crank arm with **rotating handle**

MH_{MEP} Thermoplastic glass fiber reinforced

- Arm with rotating handle
- Operating elements
- Material:
Black glass fibre reinforced polyamide
Matt surface finish




Options

- Alternative bores on request
- Industry standard keyways available

Modifiable bore



Price (tome  p.108)



DISCOUNTS

Qty	1+	10+	20+
Disc. List		-5%	On request

Part number	G	L	ØA	ØD	E	H	Prebored Ød	MEP	n	Stock*	Price each 1 to 9
MH65-MEP	65	87	18	27	10	33	4	21x50	M6	✓	20,10 €
MH80-MEP	80	105	22	30	10	36	4	21x50	M6	✓	22,92 €
MH100-MEP	100	128	24	34	10	40	4	23x70	M8	✓	26,22 €
MH130-MEP	130	162	28	40	14	49	6	26x90	M8	✓	37,00 €
MH160-MEP	160	196	34	45	15	55	6	26x90	M10	✓	46,82 €

*Depending on availability - Dimensions in mm




Crank arm with rotating handle

Square bore, thermoplastic glass fiber reinforced **MHQ_{MEP}**

- Crank arm with rotating handle and a square through-bored hole
- Operating elements
- Material:
Black glass fibre reinforced polyamide
Matt surface finish

Options

- Alternative bores on request
- Industry standard keyways available



DISCOUNTS

Qty	1+	10+	20+
Disc.	List	-5%	On request

Part number	G	L	ØA	ØD	H	T	B	C	MEP	n	Stock*	Price each
												1 to 9
MHQ65-MEP	65	87	18	27	23	8x8	20	16	21x50	M6	✓	21,00 €
MHQ80-MEP	80	105	22	30	26	10x10	22	19	21x50	M6	✓	23,47 €
MHQ100-MEP	100	128	24	34	30	12x12	27	22	23x70	M8	✓	27,90 €
MHQ130-MEP	130	162	28	40	35	14x14	30	25	26x90	M8	✓	37,39 €
MHQ160-MEP	160	196	34	45	40	17x17	34	28	26x90	M10	✓	48,54 €

*Depending on availability - Dimensions in mm

Crank arm with **folding rotating handle**

MH_{PGR} Thermoplastic glass fiber reinforced

- Crank arm with folding rotating handle
- Operating elements
- Material:
Black glass fibre reinforced polyamide
Matt surface finish




Options

- Alternative bores on request
- Industry standard keyways available

Modifiable bore



Price (tome **1** p.108)



DISCOUNTS

Qty	1+	10+	20+
Disc.	List	-5%	On request

Part number	G	L	L1	ØA	ØD	E	H	Prebored Ød	PGR	n	Stock*	Price each 1 to 9
MH80-PGR	80	105	55	22	30	10	36	4	21x50	M5	-	66,29 €
MH100-PGR	100	128	63	24	34	10	40	4	23x70	M6	✓	67,12 €
MH130-PGR	130	162	74	28	40	14	49	6	23x70	M6	-	78,17 €
MH160-PGR	160	196	86	34	45	15	55	6	26x90	M6	✓	87,14 €

*Depending on availability - Dimensions in mm