


- Male/female sleeve
- Materials:
 - Galvanised steel
 - 303 Stainless steel
- Supplied by the pack



DISCOUNTS

Qty	1+	5+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	OF	OT	S	L	X	Y	Qty per pack	Price each 1 to 4
Steel								
MHX6-8-19/B	M6	M8	13	19	7	7	20	15,91 €
MHX8-6-20/B	M8	M6	13	20	8	7	20	15,91 €
MHX8-10-23/B	M8	M10	13	23	8	9	20	15,91 €
MHX8-12-23/B	M8	M12	17	23	8	8	20	22,37 €
MHX10-6-21/B	M10	M6	13	21	8	7	20	15,91 €
MHX10-8-21/B	M10	M8	13	21	8	7	20	15,91 €
MHX10-12-25/B	M10	M12	17	25	10	8	20	22,37 €
MHX10-16-32/B	M10	M16	24	32	10	13	20	57,85 €
MHX12-8-23/B	M12	M8	13	23	10	7	20	15,91 €
MHX12-10-23/B	M12	M10	13	23	10	8	20	15,91 €
MHX12-16-32/B	M12	M16	24	32	10	13	20	57,85 €
MHX16-10-32/B	M16	M10	19	32	14	9	20	34,71 €
MHX16-12-32/B	M16	M12	19	32	14	10	20	34,71 €
Stainless steel								
MHX6-8-19/SS/B	M6	M8	13	19	7	7	20	67,94 €
MHX8-6-20/SS/B	M8	M6	13	20	8	7	20	67,94 €
MHX8-10-23/SS/B	M8	M10	13	23	8	9	20	67,94 €
MHX8-12-23/SS/B	M8	M12	17	23	8	8	20	87,92 €
MHX10-6-21/SS/B	M10	M6	13	21	8	7	20	67,94 €
MHX10-8-21/SS/B	M10	M8	13	21	8	7	20	67,94 €
MHX10-12-25/SS/B	M10	M12	17	25	10	8	20	87,92 €
MHX10-16-32/SS/B	M10	M16	24	32	10	13	20	142,29 €
MHX12-8-23/SS/B	M12	M8	13	23	10	7	20	67,94 €
MHX12-10-23/SS/B	M12	M10	13	23	10	8	20	67,94 €
MHX12-16-32/SS/B	M12	M16	24	32	10	13	20	142,29 €
MHX16-10-32/SS/B	M16	M10	19	32	14	9	20	100,82 €
MHX16-12-32/SS/B	M16	M12	19	32	14	10	20	100,82 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Our other products



H1

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



HTD14M_85

HTD Heavy duty
timing pulley, HTD14
Steel



UCF

Cast iron flange
bearing unit, Cast iron



CHMR90

Worm and wheel gear
reducer, up to 540
Nm



CHV

Mechanical speed
variator, from 0,18 to
1,5kW



CFS

Miniature cam
follower, Miniature



BKGS

Backlash free
coupling Gerwah®,
from 1.2 to 450Nm



SH1

Parallel axis helical
gear, Steel 20NCD2



MAX26

Motor-gearbox 12V
and 24V DC, from



GMK17_RG

Joint for guiding
profile, Rounded



KB_UU

Closed linear
precision bearing,



RCX-6

Spherical tilt washer -
DIN6319, convex

Complementary products



MXHred

Reducing sleeve
male/female,
Hexagonal - steel



TIF

Threaded rod -
DIN975, Stainless
steel A2



TIFss

Threaded stud -
DIN976A, Stainless
steel



MCL

Cylindrical threaded
sleeve, Cylindrical -
stainless steel