


- Male/female sleeve
- Materials:
 - Galvanised steel
 - 303 Stainless steel
- Supplied by the pack



DISCOUNTS

Qty	1+	5+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	OF	OT	S	L	X	Y	Qty per pack	Price each 1 to 4
Steel								
MHX6-8-19/B	M6	M8	13	19	7	7	20	15,91 €
MHX8-6-20/B	M8	M6	13	20	8	7	20	15,91 €
MHX8-10-23/B	M8	M10	13	23	8	9	20	15,91 €
MHX8-12-23/B	M8	M12	17	23	8	8	20	22,37 €
MHX10-6-21/B	M10	M6	13	21	8	7	20	15,91 €
MHX10-8-21/B	M10	M8	13	21	8	7	20	15,91 €
MHX10-12-25/B	M10	M12	17	25	10	8	20	22,37 €
MHX10-16-32/B	M10	M16	24	32	10	13	20	57,85 €
MHX12-8-23/B	M12	M8	13	23	10	7	20	15,91 €
MHX12-10-23/B	M12	M10	13	23	10	8	20	15,91 €
MHX12-16-32/B	M12	M16	24	32	10	13	20	57,85 €
MHX16-10-32/B	M16	M10	19	32	14	9	20	34,71 €
MHX16-12-32/B	M16	M12	19	32	14	10	20	34,71 €
Stainless steel								
MHX6-8-19/SS/B	M6	M8	13	19	7	7	20	67,94 €
MHX8-6-20/SS/B	M8	M6	13	20	8	7	20	67,94 €
MHX8-10-23/SS/B	M8	M10	13	23	8	9	20	67,94 €
MHX8-12-23/SS/B	M8	M12	17	23	8	8	20	87,92 €
MHX10-6-21/SS/B	M10	M6	13	21	8	7	20	67,94 €
MHX10-8-21/SS/B	M10	M8	13	21	8	7	20	67,94 €
MHX10-12-25/SS/B	M10	M12	17	25	10	8	20	87,92 €
MHX10-16-32/SS/B	M10	M16	24	32	10	13	20	142,29 €
MHX12-8-23/SS/B	M12	M8	13	23	10	7	20	67,94 €
MHX12-10-23/SS/B	M12	M10	13	23	10	8	20	67,94 €
MHX12-16-32/SS/B	M12	M16	24	32	10	13	20	142,29 €
MHX16-10-32/SS/B	M16	M10	19	32	14	9	20	100,82 €
MHX16-12-32/SS/B	M16	M12	19	32	14	10	20	100,82 €

Dimensions in mm

0 825 88 6000
 Service 0,15 € / min
 + prix appel

Our other products




PSG1

Spur gear - precision range, Pre-hardened Steel 35NCD6



FRss

Stainless steel thread inserts, Stainless steel



AC

Strike for toggle latch, 20mm



PRF-SCL

Lock for aluminium profile, Lock for sliding doors



COA-COG

Surface mounting plate, Surface mounting plate for ball joint



PFC

Fixed rubber levelling foot, Levelling support for small parts



MFB_MHB

Moulded plastic bevel gear (nylon), 4:1



PRF-SRA

Lock for aluminium profile, Lock



WS10

Drylin® W rail, Rail



SVG

Adjustable latch clamp with strike



CHTRP

Single and dual output gearboxes, Up



CHAFR-MINI

Miniature friction hinge, Friction

Complementary products



MHXred

Reducing sleeve male/female, Hexagonal - steel



TIF

Threaded rod - DIN975, Stainless steel A2



TIFss

Threaded stud - DIN976A, Stainless steel



MCL

Cylindrical threaded sleeve, Cylindrical - stainless steel