


- Tube for building structures
- Materials: Stainless steel or anodised aluminium
- Square tube 25 x 25mm

Accessories

- Product guide (tome 5 p.267)



DISCOUNTS

Qty	1+	10+	21+
Disc.	List	-5%	On request

Part number	Material	H	W	Length (mm)	Weight (kg/m)	Stock*	Price each 1 to 9
TUBE25-25/SS	Stainless steel	25	25	3000	3,21	-	84,20 €
TUBE25-25/AL	Aluminium	25	25	3000	1,09	-	57,89 €

*Depending on availability - Dimensions in mm

Structural fixing support





EFTC

Stainless steel

- Fixing support for square section tube
- Material: stainless steel 304

Accessories

- Tube TUBE25-25 (tome 5 p.269)



Typical application

DISCOUNTS

Qty	1+	10+	21+
Disc.	List	-5%	On request

Part number	L	Weight (kg)	Stock*	Price each 1 to 9
EFTC25-50/SS	50	0,09	-	11,09 €
EFTC25-100/SS	100	0,15	-	11,98 €
EFTC25-150/SS	150	0,20	-	13,05 €

*Depending on availability - Dimensions in mm



Square tube connector

Plastic

NCTA
NCTB

- For square tube $\square 25 \times 25 \times 1.5$ mm
- Material: reinforced polyamide

Info.

- Not sold individually, please contact us for details

Accessories


- Tube for structure TUBE (tome 5 p.269)



Type A



Type B



DISCOUNTS

Qty	1+	20+	30+
Disc.	List	-10%	On request

Part number	Weight (kg)	Type	Stock*	Price each 1 to 19
NCT25-25A	0,05	A	✓	9,97 €
NCT25-25B	0,07	B	✓	11,16 €

*Depending on availability - Dimensions in mm

Square tube connector



NCT_C
NCT_D

Plastic

- For square tube $\square 25 \times 25 \times 1.5$ mm
- Material: reinforced polyamide

Info.

- Not sold individually, please contact us for details

Accessories


- Tube for structure TUBE (tome 5 p.269)



Type C



Type D



DISCOUNTS

Qty	1+	20+	30+
Disc.	List	-10%	On request

Part number	Weight (kg)	Type	Stock*	Price each 1 to 19
NCT25-25C	0.09	C	✓	11.09 €
NCT25-25D	0.07	D	✓	10.87 €

*Depending on availability - Dimensions in mm



Square tube connector

Plastic

NCT^E
NCT^F

- For square tube $\square 25 \times 25 \times 1.5$ mm
- Material: reinforced polyamide

Info.

- Not sold individually, please contact us for details

Accessories


- Tube for structure TUBE (tome 5 p.269)



Type E



Type F



DISCOUNTS

Qty	1+	20+	30+
Disc.	List	-10%	On request

Part number	Weight (kg)	Type	Stock*	Price each 1 to 19
NCT25-25E	0,09	E	✓	11,09 €
NCT25-25F	0,11	F	✓	11,56 €

*Depending on availability - Dimensions in mm

Square tube connector



NCT_G
NCT_H

Plastic

- For square tube $\square 25 \times 25 \times 1.5$ mm
- Material: reinforced polyamide

Info.

- Not sold individually, please contact us for details

Accessories


- Tube for structure TUBE (tome 5 p.269)



Type G



Type H



DISCOUNTS

Qty	1+	20+	30+
Disc.	List	-10%	On request

Part number	Weight (kg)	Type	Stock*	Price each 1 to 19
NCT25-25G	0.13	G	-	12.47 €
NCT25-25H	0.05	H	✓	9.97 €

*Depending on availability - Dimensions in mm



Variable angle connector

Plastic

NCTAT

- For square tube $\varnothing 25 \times 25 \times 1.5$ mm
- Materials:
Body: reinforced polyamide
Screws: stainless steel

Info.


- Not sold individually, please contact us for details

Accessories


- Tube for structure TUBE (tome 5 p.269)



Adjustable



Example of use



DISCOUNTS

Qty	1+	20+	30+
Disc.	List	-10%	On request

Part number	Weight (kg)	Type	Stock*	Price each 1 to 19
NCT25-25AT	0.12	AT	✓	12,14 €

*Depending on availability - Dimensions in mm