Screen support for aluminium profile

Basic support

PRFSCREEN


- ***Swivel screen support***
- *Can be fixed in the slot or on the end of a* **PRF4545** *aluminium profile, or other profiles with 8mm or 10mm grooves*
- *For screens conforming to VESA75 and VESA100 mounting standards*
- *Materials:*
  Support plate - PA plastic reinforced glass fibre
  Hinge - PA plastic reinforced glass fibre
  Steel screws and bolts





Advantages

- *Easy to install on an aluminium profile*
- *Can be mounted horizontally or vertically for optimised visibility*
- *Precision finish for maximum strength*



DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Max load (kg)	N	Weight (g)	Stock*	Price each 1 to 2
PRF-SCREEN-1	4,9	8 - 10	200	✔	121,23 €

**Depending on availability - Dimensions in mm*

Screen support for aluminium profile


PRFSCREEN — Support with 4 axes of rotation


- ***Screen support on articulated arm***
- *Can be fixed in the slot or on the end of a* ***PRF4545*** *aluminium profile, or on a fixed support*
- *360° rotation on the vertical axis*
- *For screens conforming to VESA75 and VESA100 mounting standards*
- *Materials :*
  - *Removable VESA mounting plate - Steel/Plastics*
  - *Screen holder - Cast aluminium, lacquered*
  - *Support plate - Cast aluminium, lacquered*
  - *Adapter - Cast aluminium, lacquered*
  - *Cable cover - Black plastic*
  - *Bearings and washers - Black plastic*
  - *Zinc-plated steel screws*



Advantages

- *Easy to install on an aluminium profile*
- *Adjusts in all directions for optimum visibility*
- *Careful finishing for maximum strength*





DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Max load (kg)	Weight (g)	Price each 1 to 2
PRF-SCREEN-4	2 - 10	2200	391,52 €

Dimensions in mm

Screen support for aluminium profile

Support with 5 axes of rotation — PRFSCREEN


- ***Screen support on articulated arm***
- *Can be fixed in the slot or on the end of a* **PRF4545** *aluminium profile, or on a fixed support*
- *360°rotation on the vertical axis*
- *For screens conforming to VESA75 and VESA100 mounting standards*
- *Materials :*
  - *Removable VESA mounting plate - Steel/Plastics*
  - *Screen holder - Cast aluminium, lacquered*
  - *Support plate - Cast aluminium, lacquered*
  - *Adapter - Cast aluminium, lacquered*
  - *Cable cover - Black plastic*
  - *Bearings and washers - Black plastic*
  - *Zinc-plated steel screws*





Advantages

- *Easy to install on an aluminium profile*
- *Adjusts in all directions for optimum visibility*
- *Precision finish for maximum strength*



DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part number	Max load (kg)	Weight (g)	Price each 1 to 2
PRF-SCREEN-5	2 - 10	2930	451,94 €

Dimensions in mm