

Indexing pin for sheet metal

Stock

PPD

For thin sheets or walls

- With or without possibility to lock in open position

- Material:


Polyamide knurled knob,

mat surface finish

Body: Chromed steel


Pin: stainless steel

Position of thin wall




Info.

- Locking version: pull and turn to lock.



Typical application:
locking



DISCOUNTS

Qty	1+	6+	20+
Disc.	List -10%	On request	

Part number	Ød1	Ød2	L	H	L1	L2	ØD	Y	Y1	P	Weight (g)	Price each	
												Stock*	1 to 5
Non-locking													
PPD6-8	26	6	9	23	8,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	24,52 €
PPD6-10	26	6	9	23	10,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	24,52 €
PPD8-10	32	8	8	28	10,0	7,5	12x1,5	16	18	from 1 to 5	62	✓	26,97 €
PPD8-12	32	8	8	28	12,0	7,5	12x1,5	16	18	from 1 to 5	65	✓	26,97 €
Locking													
PPD6-8/A	26	6	9	23	8,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	24,52 €
PPD6-10/A	26	6	9	23	10,5	6,0	10x1,0	14	16	from 1 to 5	40	✓	24,52 €
PPD8-10/A	32	8	10	28	10,0	7,5	12x1,5	16	18	from 1 to 5	62	-	26,97 €
PPD8-12/A	32	8	10	28	12,0	7,5	12x1,5	16	18	from 1 to 5	65	✓	26,97 €

*Subject to availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



CHM90

Worm and wheel gear reducer, up to 540 Nm



RJUM05

Drylin R® linear bearing housing, Closed - Long



PRES

Manual workbench press accessory for PRES-3HR end PRES-4HR, Micromet...



APB_T

Adjusting rod for clamp - Female, Bored




RURp

Fixed castor with plate, Polyurethane - Aluminium rim (Free running)




D-PAR_SS

Stainless steel elastomeric mount, stainless steel



LAT1

1A motorised linear actuator, 1 ampere



HBM

Adjustment bushing for half-rail guide, Adjustment bushing



GCL

Linear ball slide - Stainless steel balls, Chariot - from 516 N



BLHM60

Right angled gearbox, double output shafts, up to 70 Nm



PLN

Cylindrical spacer, Thermoplastic



ZG2

Plastic spur gear, Machined plastic (delrin)

Complementary products



PPF

Indexing plunger with flange, with drilled flange



BIMSS

Indexing plunger mini, miniature - Stainless steel



BIM

Indexing plunger mini, miniature