

Index plunger



With horizontal flange

PPG
PPH

- **Mounting flange with screw holes**
- **Materials:**
 - Body: Zamak with black plastic coating
 - Pin: Stainless steel i.4305
 - Button : PA6 with black matt finish
- **Working temp range:** -30 /+80 °C

Info

- For the locking version, if the button is pulled and turned through 90°, the pin retained by a notch



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Locking	ØD1	ØD2	B1	B2	B3	B4 (-0,2)	h1	h2
PPG4-16-22	Without	4	12	16,5	22	6	3,3	4	7
PPG5-22-28	Without	5	16	22	28	8	4,3	4,5	9,5
PPG6-27-32	Without	6	18	27,5	32	10	5,4	5	10,5
PPG8-33-34	Without	8	21	33	34	12	5,4	6	12,5
PPH4-19-22	With	4	12	19	22	6	3,3	4	7
PPH5-25-28	With	5	16	25,5	28	8	4,3	4,5	9,5
PPH6-30-32	With	6	18	30,5	32	10	5,4	5	10,5
PPH8-37-34	With	8	21	37,5	34	12	5,4	6	12,5

Part number	K1 (+/-0,05)	K2	K3	K4	L1	L2	Pressure F1 (N)	Weight F2 (N)	Price each 1 to 5	
PPG4-16-22	14	4	8	4,5	30,5	4	3	12	11	7,44 €
PPG5-22-28	18	5	10	7	40	5	5	24	20	7,98 €
PPG6-27-32	21	5,5	12	10	49	6	5	21	37	9,16 €
PPG8-33-34	23	5,5	12	15,5	59	8	6	22	61	10,29 €
PPH4-19-22	14	4	8	4,5	33	4	3	12	10	7,49 €
PPH5-25-28	18	5	10	10,5	43,5	5	5	24	26	7,98 €
PPH6-30-32	21	5,5	12	13	52	6	5	21	40	9,16 €
PPH8-37-34	23	5,5	12	20	63,5	8	6	22	67	10,37 €

Dimensions in mm

Our other products



VHEH

Hexagonal headed screw with collar
Hygienic Usit®,
Stainless steel



TBbutee

Axial thrust bearing,
Steel balls




CDR

Retaining cable for
ball pin, Retaining
cable



RBG

Wheel, Grey rubber -
Polypropylene rim



TBV

Manual lifting tables,
3kg




INS_SS

Self tapping stainless
steel insert, 316
stainless steel



PAL

Self locking counter
nut, For axial locking



PM4

Worm and wheel set,
Machined plastic
(delrin)



SLB

Indexing plunger,
stainless steel



PAMF80EB

Articulated foot with
sheet metal base
Ø80, Articulated foot



CF

Cam follower,
Standard - steel



HRV

V- rail guidance
Simple Select®
system, Rail with
carriage

Complementary products



PPJ

Indexing plunger with
flange, With
horizontal mounting
flange and pu...



SLBW

Indexing plunger,
weldable, Weldable -
Steel