

# Tensioner pulley

Stock

## PTGR

For **round belts**

### - Idler pulley

#### - Materials:


PA6 reinforced with 30% fibreglass

Steel bearing

- Max speed 5,000 RPM

### Accessories

- AXTR shaft (tome 4 p.149)



### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request


Part number	For round belt	ØD	Width L	ØB	Bearing	C	ØA	E	G	For shaft	Stock*	Price each 1 to 9
PTGR62-10-17	Ø10	76	18	62	6203 2ZZ	38	17	10,3	12	AXTR-M12	✓	15,87 €
PTGR89-14-17	Ø14	105	18	89	6203 2RS	38	17	14,3	12	AXTR-M12	✓	18,20 €
PTGR95-11-17	Ø11	114	20	95	6203 2RS	38	17	11,3	12	AXTR-M12	✓	21,85 €

\*Depending on availability - Dimensions in mm

- Idler pulley
- Material:  
PA6 reinforced with 30% fibreglass  
steel bearing
- Max speed 5,000 RPM

### Accessories

- AXTR shaft (tome 4 p.149)



### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	For V belt	ØD	Width L	ØB	Bearing	C	ØA	E	G	For shaft	Stock*	Price each 1 to 9
PTGT49-13-17	A	76	17	49	6203 2RS	38	17	13,3	12	AXTR-M12	✓	13,98 €
PTGT75-13-17	SPA	102	17	75	6203 2RS	38	17	12,8	12	AXTR-M12	✓	15,62 €
PTGT96-15-17	XPB	127	20,5	96	6203 2RS	38	17	15,8	12	AXTR-M12	✓	20,96 €

\*Depending on availability - Dimensions en mm

# Tensioner pulley

Stock

## PTGP

For flat belts

### - Idler pulley

#### - Material:

PA6 reinforced with 30% fibreglass


Steel bearing

#### - Max speed 5,000 RPM

(Except for PTGP30 and PTGP32/9,000 RPM)

### Accessories

- AXTR shaft (tome 4 p.149)



### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-20%	-30%	On request


Part number	ØD	Width		ØB	Bearing	ØC	ØA	E	G	For shaft	Stock*	Price each
		L										1 to 9
PTGP30-9-8	40	15		30	608 ZZZ	20	8	9,2	7	AXTR-M8	✓	11,71 €
PTGP32-13-8	42	19		32	608 ZZZ	22	8	13,2	7	AXTR-M8	✓	11,84 €
PTGP50-18-17	62	24		50	6203 2RS	38	17	18,3	12	AXTR-M12	✓	12,79 €
PTGP50-20-17	62	26		50	6203 2RS	38	17	20,3	12	AXTR-M12	✓	15,78 €
PTGP75-25-17	87	30,5		75	6203 2RS	38	17	25,3	12	AXTR-M12	✓	16,95 €
PTGP75-31-17	87	36,5		75	6203 2RS	38	17	31,3	12	AXTR-M12	✓	16,12 €
PTGP75-31-17D	87	36,5		75	6203 2RS	38	17	31,3	24	AXTR-M12	✓	20,90 €

\*Depending on availability - Dimensions in mm

- Shaft for idler pulley
- Material:  
Zinc plated C45 steel

### Accessories

- Compatible with PTGP, PTGT and PTGR tensioner pulleys (tome 4 p.146, p.147, p.148)



### DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-20%	-30%	On request

Part number	ØM	ØSD	ØD	L	L1	L2	E	Across faces			Stock*	Price each 1 to 9
								SW	H			
AXTR-M8	M8	8	12	30	25	14,5	4	13	5		✓	7,92 €
AXTR-M12	M12	17	23	53	47	26,5	9	22	6		✓	7,59 €

\*Depending on availability - Dimensions in mm