


For P and PF gearboxes

PX
PDX


- **Optional accessory for adding outputs shafts**
to P and PF gearboxes

Composition


- Single sided shaft kit P-X: Stainless steel 303 shaft, 2 steel keys and 2 steel circlips
- Double sided shaft kit P-dx: Stainless steel 303 shaft, 3 steel keys and 2 steel circlips




Single sided shaft P-X



Double sided shaft P-DX



Single sided Double sided
Typical applications



DISCOUNTS

Qty	1+	2+	4+	6+
Disc.	List	-10%	-15%	On request

Part number	For gearbox								Stock*	Price each
	ØD	O/L	M	P	X	L	K			
Single sided										
P20-X	P20-PF20	6	50,80	22	23,60	3,00	25	K2 x 22	✓	39,49 €
P30-X	P30-PF30	8	63,90	28	29,80	3,00	32	K2 x 22	✓	46,41 €
P40-X	P40-PF40	10	76,60	32	34,20	3,50	40	K3 x 20	✓	52,16 €
P45-X	P45-PF45	12	88,10	38	40,20	4,00	45	K4 x 25	-	56,03 €
P55-X	P55-PF55	15	101,10	46	48,20	4,00	50	K5 x 30	-	62,06 €
P60-X	P60-PF60	20	119,80	54	56,60	4,50	60	K6 x 32	-	72,95 €
P70-X	P70-PF70	25	135,80	60	62,60	4,50	70	K8 x 40	-	83,83 €
Double sided										
P20-DX	P20-PF20	6	73,60	22	23,60	1,50	25	K2 x 22	-	52,00 €
P30-DX	P30-PF30	8	93,80	28	29,80	5,45	32	K2 x 22	-	56,52 €
P40-DX	P40-PF40	10	114,20	32	34,20	9,90	40	K3 x 20	-	64,73 €
P45-DX	P45-PF45	12	130,20	38	40,20	4,00	45	K4 x 25	-	70,73 €
P55-DX	P55-PF55	15	148,20	46	48,20	9,90	50	K5 x 30	-	77,07 €
P60-DX	P60-PF60	20	176,60	54	56,60	4,50	60	K6 x 32	-	89,62 €
P70-DX	P70-PF70	25	202,50	60	62,60	4,50	70	K8 x 40	-	102,16 €

Dimensions in mm


Our other products



SSG1_304L
Stainless steel spur gear, Stainless steel 304L



PW_PWG15
Wheel - precision range, Bronze



M1
Worm and wheel set, Machined plastic (delrin)



LTV
Miniature motorised actuator 4A, 4 ampers



SLB
Indexing plunger, steel class 5.8



HSS
Shoulder screw ISO7379, Hardened Steel class 12.9




LRRAC
Latch with locking system, Aluminium



RTZY
Diabolo shaped elasto mount, Steel



MFBC
Flexible Bellows coupling, Aluminium and Bronze - with clamping jaw



T0
Torsion spring, Stainless steel



G2
Steel spur gear, Steel 20NCD2




RPCplss
Swivel castor with double brake, Stainless steel - Polyamide

Complementary products



P15
Worm and wheel gear reducer, up to 3,75 Nm



PF15
Worm and wheel gear reducer, up to 3,75 Nm