


For P and PF gearboxes

PX
PDX


- **Optional accessory for adding outputs shafts**
to P and PF gearboxes

Composition

- Single sided shaft kit P-X: Stainless steel 303 shaft, 2 steel keys and 2 steel circlips
- Double sided shaft kit P-dx: Stainless steel 303 shaft, 3 steel keys and 2 steel circlips




Single sided shaft P-X



Double sided shaft P-DX



Single sided Double sided
Typical applications



DISCOUNTS

Qty	1+	2+	4+	6+
Disc.	List	-10%	-15%	On request

Part number	For gearbox								Stock*	Price each
	ØD	O/L	M	P	X	L	K			
Single sided										
P20-X	P20-PF20	6	50,80	22	23,60	3,00	25	K2 x 22	✓	39,49 €
P30-X	P30-PF30	8	63,90	28	29,80	3,00	32	K2 x 22	✓	46,41 €
P40-X	P40-PF40	10	76,60	32	34,20	3,50	40	K3 x 20	✓	52,16 €
P45-X	P45-PF45	12	88,10	38	40,20	4,00	45	K4 x 25	-	56,03 €
P55-X	P55-PF55	15	101,10	46	48,20	4,00	50	K5 x 30	-	62,06 €
P60-X	P60-PF60	20	119,80	54	56,60	4,50	60	K6 x 32	-	72,95 €
P70-X	P70-PF70	25	135,80	60	62,60	4,50	70	K8 x 40	-	83,83 €
Double sided										
P20-DX	P20-PF20	6	73,60	22	23,60	1,50	25	K2 x 22	-	52,00 €
P30-DX	P30-PF30	8	93,80	28	29,80	5,45	32	K2 x 22	-	56,52 €
P40-DX	P40-PF40	10	114,20	32	34,20	9,90	40	K3 x 20	-	64,73 €
P45-DX	P45-PF45	12	130,20	38	40,20	4,00	45	K4 x 25	-	70,73 €
P55-DX	P55-PF55	15	148,20	46	48,20	9,90	50	K5 x 30	-	77,07 €
P60-DX	P60-PF60	20	176,60	54	56,60	4,50	60	K6 x 32	-	89,62 €
P70-DX	P70-PF70	25	202,50	60	62,60	4,50	70	K8 x 40	-	102,16 €

Dimensions in mm

Our other products




QNUP

Single row cylindrical roller bearing, 1 fixed inner flange and 1 fr...



CFUURSS

Cam follower stainless steel, Standard - stainless steel



BETA

Hitch pin, Hitch



GLT3-76

Telescopic drawer,



PTA100

Articulated levelling foot, pressed base Ø100, Ø 100



PM2

Worm and wheel set, Hardened steel



CHB

Double output shaft, For CHB gearbox



BAN

Angular clamp, Adjustable




PTA150

Articulated levelling foot, pressed base



PTA80ssEB

Articulated foot with sheet metal base



PRL

Wear strip for slat top chain, L profile to be



PT880

Drive sprocket for slat top chain, Range 880

Complementary products



P15

Worm and wheel gear reducer, up to 3,75 Nm



PF15

Worm and wheel gear reducer, up to 3,75 Nm