

Castor with central hole

RBGTC For medium loads up to 110kg

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Grey vulcanized rubber wheel 85°Shore (see RBG)
 - Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors

Swivel



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RBG50/TC/P	50	22	76	10	98	45	✓	3,91 €
RBG60/TC/P	60	24	85	10	110	55	✓	4,44 €
RBG80/TC/P	80	23	105	10	138	65	✓	5,71 €
RBG100/TC/P	100	26	121	10	166	75	✓	6,97 €
RBG125/TC/P	125	32	158	13	216	110	✓	10,68 €
Swivel with double lock								
RBG50/TC/PDB	50	22	76	10	172	45	4	5,79 €
RBG60/TC/PDB	60	24	85	10	172	55	4	6,00 €
RBG80/TC/PDB	80	23	105	10	188	65	✓	7,19 €
RBG100/TC/PDB	100	26	121	10	188	75	✓	10,20 €
RBG125/TC/PDB	125	32	158	13	220	110	✓	14,95 €

Dimensions in mm

Our other products



TCSH
Automatic chain tensioner, With support



CLQ assortment
Assorted feeler strips, Assorted feeler strips



GP75
Spring loaded toggle latch, Standard (GP75)



AT10 courroie
AT type timing belt, AT10 Steel cored polyurethane



PCS62
Chain sprocket - steel, 15.875 (DIN 10B-1)



GE1006
Elastic ringed latch, Hooks into a slot



BLHB30
Right angled gearbox, bored shafts, up to 4.4 Nm



PRF1932
Standard aluminium profile, 19 x 32 mm



RMSA
Adjustable shock-absorber, Adjustable



T5-16ECO
T type timing pulley, Economy range - T5 aluminium



RAGFLOW
Floway2® roller track, Roller track



MHXred
Reducing sleeve male/female, Hexagonal - stainless steel

Complementary products



RBNtc
Swivel castor with central hole, Steel - rubber



RBG
Wheel, Grey rubber - Polypropylene rim



RBGtc
Swivel castor with central hole, Steel - grey rubber - with double b...



RPCtcss
Swivel castor with central hole, Stainless steel - Polyamide