

Rubber castor with central hole

RBNTC

For heavy loads up to 215kg


- **Industrial wheel suitable for loads up to 215kg**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- **Materials:**
 - Baseplate: pressed steel sheet, protected by bright zinc plating
 - Black vulcanized rubber wheel 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C



Swivel with double locks

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Maximum load (kg)	Price each 1 to 9
Swivel							
RBN80/TC/P	80	34	105	12	158	75	9,76 €
RBN100/TC/P	100	35	125	12	182	100	10,76 €
RBN125/TC/P	125	38	152	12	210	125	13,31 €
RBN150/TC/P	150	40	179	12	242	150	17,17 €
RBN160/TC/P	160	38	188	12,5	267	150	24,29 €
RBN200/TC/P	200	47	232	12,5	320	215	29,54 €
Swivel with double lock							
RBN80/TC/PDB	80	34	105	12	290	75	14,96 €
RBN100/TC/PDB	100	35	125	12	290	100	15,80 €
RBN125/TC/PDB	125	38	152	12	290	125	18,40 €
RBN150/TC/PDB	150	40	179	12	290	150	23,29 €
RBN160/TC/PDB	160	38	188	12,5	267	150	36,40 €
RBN200/TC/PDB	200	47	232	12,5	320	215	42,12 €

Dimensions in mm

Our other products



SHW
Plain washer, A2
Stainless steel



SHN
Hexagonal nut
DIN934, Steel (Class
6[8])



ACLEFS
Floor anchor for
aluminium profile,
Adjustable



RFVcap
Stainless steel
protective cover,
Open protective cover



LC
Friction clutch, 30 to
240 Nm



AT5M AT10M
AT type timing belt
per metre, AT10 Steel
cored polyurethane



BPHF
Ball transfer unit push
fit, Heavy



OP7
Mechanical digital
position indicator, 5
numbers



GAL_20
Conveyor roller for
Ø20mm spindle, Self-
aligning



BPPE
Ball transfer unit push
fit, Light



BAC105
Storage bin, 8mm



GAL_25
Ø25 conveyor roller,
Without ball bearing

Complementary products



RBN
Wheel, Rubber tyre -
Polypropylene rim



RBGtc
Swivel castor with
central hole, Steel -
grey rubber



RBNtc
Swivel castor with
central hole, Steel -
rubber - with double
brake



RPCtc
Swivel castor with
central hole, Steel -
Polyamide