

Polyamide castor with central hole


For heavy loads up to 600kg

RPCTC

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Polyamide wheel (see RPC)
 - Working temperature range: - 30°C to + 80°C

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel							
RPC60/TC/P	60	31	97	12	140	200	8,74 €
RPC80/TC/P	80	32	106	12	160	250	9,28 €
RPC100/TC/P	100	32	124	12	184	300	9,72 €
RPC125/TC/P	125	36	152	12	210	350	14,47 €
RPC150/TC/P	150	37	181	12	246	400	20,32 €
RPC160/TC/P	160	40	189	12,5	268	500	41,09 €
RPC200/TC/P	200	50	232	12,5	318	600	47,24 €
Swivel with double brake							
RPC80/TC/PDB	80	32	106	12	290	250	14,64 €
RPC100/TC/PDB	100	32	124	12	290	300	15,37 €
RPC125/TC/PDB	125	36	152	12	290	350	19,53 €
RPC150/TC/PDB	150	37	181	12	290	400	25,66 €
RPC160/TC/PDB	160	40	189	12,5	268	500	51,83 €
RPC200/TC/PDB	200	50	232	12,5	318	600	53,78 €

Dimensions in mm

0 825 88 6000
 Service 0,15 € / min
 + prix appel

Fax

Our other products




GPLbr

Brush, brass



CQA20

Adjustment slide-system miniature, 20



M1

Worm and wheel set,
Machined plastic
(delrin)



PRF_FIX_UNI

Universal fastener for
aluminium profile,
Universal



NT91

Spur gear coaxial
gearbox, from 10 to
35 Nm - In-line



CHALss

Piano hinge, Stainless
steel



ACLCHAR

Hinge for aluminium
profile, With
elongated holes



GE_ET_2RS

Spherical bushing,
Hard chromium /
Teflon contact with
seals



EPE

Wing nuts Hygienic
Design®, Narrow



HW_HT

Half-rail guide, Rail



APB_F

Adjusting rod for
clamp - Male,
Threaded



CHINV

Invisible hinge,
Invisible - Opening up
to 90°

Complementary products



TSRTC

Stem support for
caster, For swivel
caster with central
hole



RPC

Wheel, Polyamide



RBNTc

Swivel caster with
central hole, Steel -
rubber



RBGtc

Swivel caster with
central hole, Steel -
grey rubber - with
double b...