

Free running wheel with central hole

RURT

For loads up to 350kg

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

swivel

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	On request	

Part number	ØD	H	B	A	F	E	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel									
RURT80/P	80	106	40	12	41	12	162	180	26,07 €
RURT100/P	100	126	40	12	41	12	184	220	28,42 €
RURT125/P	125	153	40	15	41	12	216	260	32,30 €
RURT150/P	150	180	40	20	50	12	244	350	32,30 €
Swivel with double brake									
RURT80/PDB	80	106	40	12	41	12	290	180	31,19 €
RURT100/PDB	100	126	40	12	41	12	290	220	33,83 €
RURT125/PDB	125	153	40	15	41	12	290	260	37,65 €
RURT150/PDB	150	180	40	20	50	12	290	350	50,18 €

Dimensions in mm

Our other products



GCB880
Curved track for slat top chain, Ranges 880 and 881



PVL
Small lobed handle, Polyamide



SCR
Suction cup threaded insert, Adaptator for insert



DOMI50
Accessories, Clamping lever



BAN
Angular clamp, Standard



BPP
Pressed steel flanged bearing for light loads, Sheet steel



VQTplqn
Quarter-turn clamp lock - Clamping plate, Flush mounting



EX
Optional shaft for E-type gear reducers, E Gearboxes single sided ou...




BH02
Single housed bearing assembly, Bearing



BFA
Shaft locking washer, E clip



RAGb
Cylindrical brush track, For gentle



CHAGC-AL
Screw-in garnet hinge, Screw-on

Complementary products



RUR
Wheel, Polyurethane - Aluminium rim (Free running)



TSRTC
Stem support for caster, For swivel caster with central hole



RURT
Swivel castor with central hole, Polyurethane - Aluminium rim (Free running)

...



RURp
Fixed castor with
plate, Polyurethane -
Aluminium rim (Free
running)