

# Stainless steel ball bearing ABEC 1


## S2RS

## With sealed joints

- Radial contact ball bearing
- Bearing with 2 sealed joints (2RS)
- Material:  
Cage + balls: stainless steel AISI 440C  
Joint: Neoprene
- Static and dynamic loads : these bearings can handle approx 70% of the same loads that an equivalent steel bearing will accept
- Max. working temperature: +80°C

### Accessories

- Nut FU-SS



### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØA	ØD	E	Stock*	Price each 1 to 5
S6000-2RS	10	26	8	✓	7,40 €
S6200-2RS	10	30	9	✓	9,30 €
S6001-2RS	12	28	8	✓	8,56 €
S6201-2RS	12	32	10	✓	10,40 €
S6301-2RS	12	37	12	-	14,93 €
S6002-2RS	15	32	9	✓	10,34 €
S6202-2RS	15	35	11	✓	12,42 €
S6302-2RS	15	42	13	-	21,11 €
S6003-2RS	17	35	10	-	15,91 €
S6203-2RS	17	40	12	-	17,31 €
S6303-2RS	17	47	14	-	25,21 €
S6004-2RS	20	42	12	✓	17,99 €
S6204-2RS	20	47	14	-	19,95 €
S6304-2RS	20	52	15	-	27,17 €
S6005-2RS	25	47	12	✓	24,35 €
S6205-2RS	25	52	15	-	29,13 €
S6305-2RS	25	62	17	-	45,04 €
S6006-2RS	30	55	13	✓	30,96 €
S6306-2RS	30	72	19	-	63,89 €
S6007-2RS	35	62	14	-	38,92 €
S6207-2RS	35	72	17	-	57,28 €
S6208-2RS	40	80	18	-	76,31 €

\*Depending on availability - Dimensions in mm

## Our other products



PITAss

Locking bolt, with T handle



BG

Oldham coupling, With set screw



CHB

Worm and wheel gear reducer, up to 41 Nm



SA\_SAKH

Housing for linear bearing, Closed - light load



SHS

Shoulder screw stainless steel 303, Stainless steel 303



BIM

Indexing plunger mini, miniature



VDS

Sliding lock adjustment system, Sliding lock for oblong hole



Q6

Deep groove ball bearing, Steel



DBL805

Idle for slat top chain, Range 805



PW\_PWG15

Wheel - precision range, Bronze



CHM90

Worm and wheel gear reducer, up to 540 Nm



PSG155

Spur gear - precision range, Stainless steel 316

## Complementary products



S\_ZZ

Deep groove ball bearing, Stainless steel



SF\_ZZ

Deep groove ball bearing, Stainless steel



FUSS

Bearing locknut, Self locking locknut - stainless steel lock washer