

Flat cable clamp







SCA

Suitable for cable Ø2-Ø6mm

- Fitting components
- Flat cable clamp, with single or dual
- Material:
Clamp: Zinc plated steel Fe360B

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	3+	6+	9+	12+	15+
Disc.	List	-5%	-10%	-15%	-20%	On request


Part number	Ø Cable	A	B	C	E	F	Weight per 100 pieces (kg)	Qty per packet	Stock*	Price each 1 to 2
Single										
SCA1-02/B	2	18	12	5	8	-	0,50	10	✓	4,84 €
SCA1-03/B	3	20	14	7	10	-	0,75	10	✓	6,74 €
SCA1-04/B	4	22	17	8	12	-	1,15	10	✓	7,66 €
SCA1-05/B	5	26	21	9	14	-	2,00	10	✓	9,46 €
SCA1-06/B	6	30	25	10	17	-	3,00	10	✓	10,26 €
Dual										
SCA2-02/B	2	37	13	5	8	20	1,10	10	✓	8,49 €
SCA2-03/B	3	40	15	7	10	21	1,50	10	✓	9,46 €
SCA2-04/B	4	43	17	7	13	22	2,50	10	✓	10,75 €
SCA2-05/B	5	52	22	9	15	27	4,00	10	✓	17,01 €
SCA2-06/B	6	60	26	9	18	33	6,00	10	✓	19,49 €

*Depending on availability - Dimensions in mm

- **Fitting components**
- Flat cable clamp, single or dual
- **Material:**
Clamp: Stainless steel 316 plated steel Fe360B

Info.

- Sold by the packet

**DISCOUNTS**

Qty	1+	3+	6+	9+	12+	15+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	Ø Cable	A	B	C	E	F	Weight per 100 pieces (kg)	Qty per packet	Stock*	Price each 1 to 2
Single										
SCA1-02/SS/B	2	15	11	5,0	7	-	0,438	4	✓	5,57 €
SCA1-03/SS/B	3	17	14	6,0	9	-	0,520	4	✓	7,17 €
SCA1-04/SS/B	4	20	17	7,0	11	-	1,090	4	✓	8,78 €
SCA1-05/SS/B	5	25	19	8,5	13	-	1,442	4	-	11,86 €
SCA1-06/SS/B	6	30	24	10,0	16	-	2,630	4	✓	19,33 €
Dual										
SCA2-02/SS/B	2	30	11	5,0	7	15	0,926	4	✓	9,16 €
SCA2-03/SS/B	3	34	14	6,0	9	17	1,230	4	✓	12,19 €
SCA2-04/SS/B	4	40	17	7,0	11	19	2,290	4	✓	16,70 €
SCA2-05/SS/B	5	50	19	8,5	13	25	3,090	4	✓	21,12 €
SCA2-06/SS/B	6	60	24	10,0	16	30	5,440	4	✓	29,71 €

*Depending on availability - Dimensions in mm