



- Fitting elements
- Flat cable clamp with single or dual bolts
- Material:
Clamp: Stainless steel 316 plated steel Fe360B

Info.

- Not sold individually, please contact us for details



Single bolt



Dual bolts

DISCOUNTS

Qty	1+	30+	60+	90+	120+	150+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	Ø Cable	A	B	C	E	F	Weight per 100 pieces (kg)	Stock*	Price each 1 to 29
Single bolts									
SCA1-02/SS	2	15	11	5,0	7	-	0,438	✓	1,19 €
SCA1-03/SS	3	17	14	6,0	9	-	0,520	✓	1,52 €
SCA1-04/SS	4	20	17	7,0	11	-	1,090	✓	1,87 €
SCA1-05/SS	5	25	19	8,5	13	-	1,442	✓	2,52 €
SCA1-06/SS	6	30	24	10,0	16	-	2,630	✓	4,09 €
Dual bolts									
SCA2-02/SS	2	30	11	5,0	7	15	0,926	✓	1,95 €
SCA2-03/SS	3	34	14	6,0	9	17	1,230	✓	2,59 €
SCA2-04/SS	4	40	17	7,0	11	19	2,290	✓	3,53 €
SCA2-05/SS	5	50	19	8,5	13	25	3,090	✓	4,48 €
SCA2-06/SS	6	60	24	10,0	16	30	5,440	✓	6,28 €

*Depending on availability - Dimensions in mm

Our other products



BTCW
Tube end cap, To be welded



ZG2
Spur gear, Machined plastic (delrin)




GBSz
Ballscrew, Cylindrical leadscrew nut



DIA
Indexing plunger, with ring



PTA150
Articulated foot with pressed base, Ø 150




RPPM
RPP type belt by the metre, RPP14 Steel cored polyurethane



BPM_LOK
Slotted spring plunger with ball tip, LONG-LOK - Stainless steel 303



BABFCFO
Ball pin, Mounting collar with a round flange



KS
Key, Steel - Keystock



BOX-TOR-DRING
Box set of Nitrile D-rings, Flange seals



T5M_T10M
Timing belt per metre, T10 Steel cored polyurethane




FF10
Offset spur gear reducer, from 0.78 to 3.70 Nm

Complementary products



SCA_SS
Cable clamp, Stainless steel



CAB
Aircraft cable, Stainless steel



CCLSS
Wire thimble, Stainless steel



PPCcs
Pad eye on mounting plate, Stainless steel