

Positioning sleeve for indexing pin New


SDC

For pin Ø4 to Ø12


- Suitable for indexing pins and indexing locks
- Low wear due to hardened cone
- Materials:
Hardened and burnished steel
Hardened stainless steel

Accessories

- Compatible with the SDA and SDB locating bolt support bracket (tome 1 p.68-69)
- Compatible with the HPC range of indexing pins.



Application example



DISCOUNTS

Qty	1+	6+	20+
Disc.	Price -10%	On request	

Part number	ØD	ØD3		ØD4		L5			For pin diam	Weight (g)	Price each 1 to 5		
		(+0,1)	ØD2	(-0,05)	L1	L2	L3	L4				(+0,5)	
Steel													
SDC12F-4	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	9,49 €
SDC12F-5	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	9,55 €
SDC12F-6	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	9,55 €
SDC16F-8	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	11,46 €
SDC16F-10	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	11,38 €
SDC16F-12	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	11,46 €
Stainless steel													
SDC12F-4/SS	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	12,75 €
SDC12F-5/SS	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	12,75 €
SDC12F-6/SS	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	12,75 €
SDC16F-8/SS	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	18,53 €
SDC16F-10/SS	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	18,53 €
SDC16F-12/SS	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	18,53 €

Dimensions in mm

Our other products



SCA_SS

Stainless steel flat cable clamp, Stainless steel




MLY_SS

Stainless steel bow shackle with eye bolt, Stainless steel



PR40

Articulated foot Ø50, Ø 50



RPP

Connecting plate for RPP type timing belts, RPP14



TBE16

Economic mini-table with trapezoidal leadscrew, 5kg



SSHBRA

Stainless steel bevel gear, 1,5:1 2:1 3:1



TBbutee

Axial thrust bearing, Steel balls



DOMI50

Accessories, Fixing kit



QTR

Tapered roller bearing, Steel



MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm



BAG-MI

Split shaft collar with clamp lever, Steel



PAMF120

Articulated fixable foot, pressed bolt-down base Ø 120, Ø 120

Complementary products



SDC

Positioning sleeve for indexing pin, For pin Ø4 to Ø12



SDA

Locking bolt support bracket, Mounting holes parallel to locating bolt



SDB

Locking bolt support bracket, Mounting holes at 90° to locating bolt



SLB

Indexing plunger, steel class 5.8