

Positioning sleeve for indexing pin New

SDC

For pin Ø4 to Ø12


- Suitable for indexing pins and indexing locks
- Low wear due to hardened cone
- Materials:
 - Hardened and burnished steel
 - Hardened stainless steel

Accessories


- Compatible with the SDA and SDB locating bolt support bracket (tome 1 p.68-69)
- Compatible with the HPC range of indexing pins.



NEW!



Application example



DISCOUNTS

Qty	1+	6+	20+
Disc.	Price -10%	On request	On request

Part number	ØD	ØD3		ØD4		L5			For pin diam	Weight (g)	Price each 1 to 5		
		(+0,1)	ØD2	(-0,05)	L1	L2	L3	L4				(+0,5)	
Steel													
SDC12F-4	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	9,49 €
SDC12F-5	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	9,55 €
SDC12F-6	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	9,55 €
SDC16F-8	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	11,46 €
SDC16F-10	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	11,38 €
SDC16F-12	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	11,46 €
Stainless steel													
SDC12F-4/SS	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	12,75 €
SDC12F-5/SS	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	12,75 €
SDC12F-6/SS	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	12,75 €
SDC16F-8/SS	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	18,53 €
SDC16F-10/SS	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	18,53 €
SDC16F-12/SS	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	18,53 €

Dimensions in mm

Our other products



FF15

Offset spur gear reducer, from 2.20 to 10 Nm




YG4

HEAVY DUTY spur gear, Steel 35NCD6



SER69K

Quarter turn latch for the food industry, Stainless steel



TBV

Manual lifting tables, 12kg



PW_PWG15

Worm - precision range, Stainless steel



M0

Worm and wheel set, Hardened steel



BPQ

Quadro linear ball bearing unit, Included 4 linear ball bearings



BPHF

Ball transfer unit push fit, Heavy



PT882

Drive sprocket for slat top chain, Range 882



ZG4

Plastic spur gear, Machined plastic (delrin)



LVT

Miniature motorised actuator 1A, 1 amper



TM_CTM_CTF

Suction cup threaded insert, Insert for suction cup - Tread click-in

Complementary products



SDC

Positioning sleeve for indexing pin, For pin Ø4 to Ø12



SDA

Locking bolt support bracket, Mounting holes parallel to locating bolt



SDB

Locking bolt support bracket, Mounting holes at 90° to locating bolt



SLB

Indexing plunger, steel class 5.8