

# Stainless steel spur gear




## Module 1.5

## 304L stainless steel



- Quality standard 9
- Pressure angle 20°

Torque and power indication				
For 50 teeth at 1000 rpm				
	StS 304L	brass	fibre	
Nm	8,88	4,44	3,55	
kW	0,93	0,46	0,37	



stainless steel

### DISCOUNTS

Qty	1+	6+	20+
Disc.	List -12%	On request	

Part number	Teeth Z	pcd ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 5
SSG1.5-12-304L	12	18	21	14	8	28,18 €
SSG1.5-15-304L	15	22,5	25,5	18	8	30,97 €
SSG1.5-16-304L	16	24	27	20	10	32,30 €
SSG1.5-18-304L	18	27	30	20	10	36,36 €
SSG1.5-20-304L	20	30	33	20	10	38,63 €
SSG1.5-22-304L	22	33	36	20	10	42,74 €
SSG1.5-24-304L	24	36	39	25	10	44,73 €
SSG1.5-30-304L	30	45	48	25	10	56,51 €
SSG1.5-32-304L	32	48	51	25	10	60,71 €
SSG1.5-36-304L	36	54	57	30	15	69,79 €
SSG1.5-40-304L	40	60	63	40	15	74,12 €
SSG1.5-44-304L	44	66	69	40	15	74,28 €
SSG1.5-46-304L	46	69	72	40	15	77,50 €
SSG1.5-48-304L	48	72	75	40	15	80,97 €
SSG1.5-50-304L	50	75	78	40	15	112,40 €
SSG1.5-54-304L	54	81	84	40	15	112,40 €
SSG1.5-56-304L	56	84	87	40	15	112,40 €
SSG1.5-60-304L	60	90	93	40	15	154,48 €
SSG1.5-64-304L	64	96	99	40	15	154,48 €
SSG1.5-66-304L	66	99	102	40	15	177,20 €
SSG1.5-70-304L	70	105	108	40	15	177,20 €



**Gears available up to this size**



SSG1.5-298-304L	298	447	450	Dimensions: contact us	on request
-----------------	-----	-----	-----	------------------------	------------

\*Depending on availability - Dimensions in mm

## Our other products



MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



MEB

Moulded plastic bevel gear (nylon), 1:1



CHM50

Worm and wheel gear reducer, up to 107 Nm




G4-ECO

Eco range Spur gear, Steel C45



GAL21

Conveyor wheel, Plastic



RPPM

RPP type belt per metre, RPP8 Steel cored polyurethane



SLB

Indexing plunger, steel class 5.8



PCF4

Conical flexible mount, Square base plate



CHAEss

Decorative hinge, Stainless steel



J51

Spur gear coaxial gearbox, from 0.13 to



GLT3-46A


Telescopic drawer with damper,



G0

Steel spur gear, Steel 20NCD2

## Complementary products



MRS

Stainless steel metric section rack, Stainless steel



TRMSS

Spur round rack, Stainless steel - module 1-5