

Articulated foot with sheet metal base Ø50

Max load: 4000N
Rubber sole in EPDM, blue


- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- **Materials:**
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

References	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA50-10-75/SS/EB	50	M10	75	29	14	19	104	4,000	17,56€
PTA50-10-125/SS/EB	50	M10	125	29	14	19	154	4,000	19,83€
PTA50-12-75/SS/EB	50	M12	75	29	14	19	104	4,000	17,56€
PTA50-12-125/SS/EB	50	M12	125	29	14	19	154	4,000	19,83€
PTA50-16-75/SS/EB	50	M16	75	34	13	19	109	4,000	20,38€
PTA50-16-100/SS/EB	50	M16	100	34	13	19	134	4,000	21,14€
PTA50-16-150/SS/EB	50	M16	150	34	13	19	184	4,000	23,13€

* Depending on availability - Dimensions in mm

Our other products



WS20
Drylin® W rail, Rail



AC156-157
Strike for toggle latch,
25.5mm



BS2
Panamech, Multi-Beam, Aluminium -
with set screw



TCC
Rigging screw
(hook/hook), Steel



VTA
Vari-Tork® slip
friction clutch, 0.53 to
1.32 Nm



DOMI120
Accessories, Fixing kit



BPVM
Miniature ball transfer
unit, Miniature to
screw



SH4
Parallel axis helical
gear, Steel 20NCD2



CHMR40
Worm and wheel gear
reducer, up to 57 Nm



RBNpl
Fixed castor with
plate, Steel - rubber



NT91
Spur gear coaxial
gearbox, from 10 to
500 Nm



CHB
Worm and wheel gear
reducer, up to 41 Nm

Complementary products



PTA80ssEB
Articulated foot with
sheet metal base
Ø80, Articulated foot



PTA100ssEB
Articulated foot with
sheet metal base
Ø100, Articulated foot



PAMF80EB
Articulated foot with
sheet metal base
Ø80, Articulated foot



PAMF100EB
Articulated foot with
sheet metal base
Ø100, Articulated foot