

Stainless steel spur gear




Module 2.0

304L stainless steel



- Quality standard 9
- Pressure angle 20°

Torque and power indication			
For 50 teeth at 1000 rpm			
	StS 304L	brass	fibre
Nm	25	12,50	10
kW	2,61	1,32	1,04



stainless steel

DISCOUNTS

Qty	1+	6+	20+
Disc.	List -12%	On request	On request

Part number	Teeth Z	pcd ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 5
SSG2-12-304L	12	24	28	28	12	42,73 €
SSG2-15-304L	15	30	34	25	15	37,01 €
SSG2-16-304L	16	32	36	25	15	39,40 €
SSG2-18-304L	18	36	40	30	15	44,70 €
SSG2-20-304L	20	40	44	30	15	47,77 €
SSG2-22-304L	22	44	48	35	15	53,72 €
SSG2-24-304L	24	48	52	35	15	59,15 €
SSG2-30-304L	30	60	64	40	20	77,10 €
SSG2-32-304L	32	64	68	40	20	79,66 €
SSG2-36-304L	36	72	76	50	20	92,60 €
SSG2-40-304L	40	80	84	50	20	148,67 €
SSG2-44-304L	44	88	92	50	20	204,32 €
SSG2-46-304L	46	92	96	50	20	204,32 €
SSG2-48-304L	48	96	100	50	20	204,32 €
SSG2-50-304L	50	100	104	50	20	234,38 €
SSG2-54-304L	54	108	112	50	20	234,38 €
SSG2-56-304L	56	112	116	50	20	267,43 €
SSG2-60-304L	60	120	124	50	20	267,43 €
SSG2-64-304L	64	128	132	50	20	304,14 €
SSG2-66-304L	66	132	136	50	20	322,97 €
SSG2-70-304L	70	140	144	50	20	336,13 €

Gears available up to this size

SSG2-290-304L	290	580	584	Dimensions: contact us	on request
---------------	-----	-----	-----	------------------------	------------

*Depending on availability - Dimensions in mm

Our other products




BLHB50

Right angled gearbox, bored shafts, up to 30 Nm



ACLBDB

Closing mechanism for aluminium profile, Dual ball catch



PF30NM

Worm and wheel gear reducer, up to 8.8 Nm




SSB

Stainless steel bevel gear, 1:1



PRF19_E

Bracket for aluminium profile, PRF19 to PRF45



BLHM40

Right angled gearbox, double output shafts, up to 10.3 Nm



CHAEpac

Square decorative screwed hinges, carbon fibre reinforced



ESCON

Speed controller 5A accessories, Kit of 4 cables for DC motor



SBRtool

Chain tool, Drive chain maintenance




DB

Steel bevel gear, 2:1



RT61ss


Self-centering locking Assembly,



B

Steel bevel gear, 1:1

Complementary products



MRS

Stainless steel metric section rack, Stainless steel



TRMSS

Spur round rack, Stainless steel - module 1-5