

Freewheel with internal bearing

Self centering

QUK
QUKC

- Transmits torque in one direction, free movement in the other
- Keyway conforms to DIN6885
- Max torque = $2 \times T_N$
- Material: steel

Assembly

- **QUK:**
Shaft tolerance n6
Housing tolerance N6
- **QUKC:**
Shaft tolerance k6
Housing tolerance N6

Info


- Self centering freewheel, pre-greased and fitted with anti-dust protection




QUK



QUKE



QUK



QUKE


DISCOUNTS

Qty	1+	6+	30+
Disc	List	-6%	On request

Part number	ØD	ØD1	b	L	(Js9)	t	Bearing type	Load capacity		Torque	Residual	Weight	Price
		(h5)							Dynamic	Static	T _N		
Without keyway													
QUK15 ZZ	15 ^{-0,01}	35	11	-	-		6202ZZ	7400	3400	16,9	0,009	0,06	38,54 €
QUK17 ZZ	17 ^{-0,01}	40	12	-	-		6203ZZ	7900	3800	30,6	0,011	0,07	34,78 €
QUK20 ZZ	20 ^{-0,01}	47	14	-	-		6204ZZ	9400	4450	50,0	0,013	0,11	39,82 €
QUK25 ZZ	25 ^{-0,01}	52	15	-	-		6205ZZ	10700	5450	85,0	0,020	0,14	41,84 €
QUK30 ZZ	30 ^{-0,01}	62	16	-	-		6206ZZ	11700	6450	138,0	0,044	0,21	52,71 €
With keyway													
QUKC15 ZZ	15H7	35	11	5	1,2		6202ZZ	7400	3400	16,9	0,009	0,06	41,69 €
QUKC17 ZZ	17H7	40	12	5	1,2		6203ZZ	7900	3800	30,6	0,011	0,07	38,06 €
QUKC20 ZZ	20H7	47	14	6	1,6		6204ZZ	9400	4450	50,0	0,013	0,11	42,65 €
QUKC25 ZZ	25H7	52	15	8	2,0		6205ZZ	10700	5450	85,0	0,020	0,14	44,34 €
QUKC30 ZZ	30H7	62	16	8	2,0		6206ZZ	11700	6450	138,0	0,044	0,21	56,31 €

Dimensions in mm

Our other products



CDRs
Ball pin, Retaining cable



PV2R
Adjustable suction-cup support, Increased grip



LWL
Linear ball slide - Stainless steel balls, Rail - from 514 N to 16700 N



SH4
Parallel axis helical gear, Steel 20NCD2



INS100
Self tapping insert, Coarse thread



PTGP
Tensioner pulley, For flat belts



BAC105
Storage bin, 8mm



ACLERP
Roller block, With guide rail




TMR
Tensioner plate, Adjustable



BCFH
Mushroom headed button Hygienic Usit®, With male



CHMR90
Worm and wheel gearbox, up to 540 Nm



B
Bevel gear - Steel 60C40, 1:1

Complementary products



HFL
Freewheel, Needle bearing



QUK
Freewheel, With internal bearing



KM
Bearing - accessories, Locknut KM



EAR
Bearing - accessories, Self locking locknut - nylon lock washer