

# Castor with central hole

## RBGTC For medium loads up to 110kg

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
  - Top plate: pressed steel sheet, protected by bright zinc plating
  - Grey vulcanized rubber wheel 85°Shore (see RBG)
  - Smooth central bore
- Working temperature range: - 20°C to + 60°C

### Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors

Swivel



ØD



B



H



ØE



ØK


### DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
<b>Swivel</b>								
RBG50/TC/P	50	22	76	10	98	45	✓	3,91 €
RBG60/TC/P	60	24	85	10	110	55	✓	4,44 €
RBG80/TC/P	80	23	105	10	138	65	✓	5,71 €
RBG100/TC/P	100	26	121	10	166	75	✓	6,97 €
RBG125/TC/P	125	32	158	13	216	110	✓	10,68 €
<b>Swivel with double lock</b>								
RBG50/TC/PDB	50	22	76	10	172	45	4	5,79 €
RBG60/TC/PDB	60	24	85	10	172	55	4	6,00 €
RBG80/TC/PDB	80	23	105	10	188	65	✓	7,19 €
RBG100/TC/PDB	100	26	121	10	188	75	✓	10,20 €
RBG125/TC/PDB	125	32	158	13	220	110	✓	14,95 €

Dimensions in mm

## Our other products



TC1rp  
Automatic chain tensioner, With 180° guide



PRF-P  
Aluminium profile feet support, For feet or casters



SCR  
Suction cup threaded insert, Insert for suction cup - Socket screw



TFR  
Rigid manual tensioner, Fixed



TOL  
Swivel head, Long



BTCW  
Cap for square tube to be welded, To be welded



HCA  
Magnetic screw with socket, Steel



BSPM  
Miniature ballscrew, Nut+rolled ballscrew



PLB  
Cylindrical spacer, Brass



GLT3E-58  
Telescopic drawer,



PDM\_PDV  
Detectable plastic palm grip, blue thermoplastic



ESCON  
Speed controller 5A accessories, Kit of 4 cables for DC motor

## Complementary products



RBG  
Wheel, Grey rubber - Polypropylene rim



RPCtc  
Swivel castor with central hole, Steel - Polyamide



RBNtc  
Swivel castor with central hole, Steel - rubber



RPCtcss  
Swivel castor with central hole, Stainless steel - Polyamide - with ...