

Spherical seating washer **DIN6319** **Ste** **DIN** **Stock**

For M6-M24 screws

RCC RCX

- Use a concave washer with a convex washer
- Material:
Treated steel, tempered,
Manganese phosphating
- Other sizes on request




RCX




RCC

Advantages


- Good distribution of clamping force
- Ensures that the screw head is in the right position



RCX convex washer



RCC concave washer



Typical application

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Net	-5%	-10%	On request

Part number	For screw	ØD1 H13	ØD3	ØD5	H1	H2	R1	Max static load (kN)	Stock*	Price each 1 to 5
Convex washer										
RCX-6	M6	6,4	12	-	0,7	2,3	9	9	✓	0,92 €
RCX-8	M8	8,4	17	-	0,6	3,2	12	17	✓	0,95 €
RCX-10	M10	10,5	21	-	0,8	4	15	26	✓	1,31 €
RCX-12	M12	13	24	-	1,1	4,6	17	38	✓	1,67 €
RCX-14	M14	15	28	-	1,4	5	22	53	-	2,38 €
RCX-16	M16	17	30	-	1,3	5,3	22	73	-	2,38 €
RCX-20	M20	21	36	-	2	6,3	27	117	-	3,60 €
RCX-24	M24	25	44	-	2,4	8,2	32	168	-	5,38 €
Concave washer										
RCC-6	M6	7,1	12	11	-	2,8	-	9	✓	0,99 €
RCC-8	M8	9,6	17	14,5	-	3,5	-	17	✓	1,10 €
RCC-10	M10	12	21	18,5	-	4,2	-	26	✓	1,38 €
RCC-12	M12	14,2	24	20	-	5	-	38	✓	1,74 €
RCC-14	M14	16,5	28	24,8	-	5,6	-	53	-	2,92 €
RCC-16	M16	19	30	26	-	6,2	-	73	-	2,92 €
RCC-20	M20	23,2	36	31	-	7,5	-	117	-	3,95 €
RCC-24	M24	28	44	37	-	9,5	-	168	-	6,02 €

* Subject to available stocks, All dimensions in mm

Our other products



AT10-50ECO

AT type timing pulley,
Economy range -
AT10 aluminium



RFK28B

Hypoid gearbox -
Stainless steel, up to
130 Nm



GSI

Stainless steel gas
spring, Stainless steel



AT5M AT10M

AT type timing belt
per metre, AT10 Steel
cored polyurethane



FHCS

Countersunk screw,
Stainless steel A2 -
DIN 7991



SCA_SS

Stainless steel flat
cable clamp, Stainless
steel



BPM

Slotted spring plunger
with ball tip, Stainless
steel 303



SH0

Parallel axis helical
gear, Machined plastic
(delrin)



DOMI80

Connecting kits, XZ
linking kit



PSG35

Spur gear - precision
range, Stainless steel



CHMR

Reaction arm, CHM
and CHMR gear



UTKswrr

V shaped channel
UtiliTrak®, V rail

Complementary products



RCX-6

Spherical tilt washer -
DIN6319, convex



RCC_RCX

Spherical tilt washer -
DIN6319, concave



RCC_RCX

Spherical tilt washer -
DIN6319, convex